

# Product data sheet

Specifications



Switch disconnecter, TeSys  
Control, for ON/OFF, 40A,  $\tilde{A}$ ~22.5  
fixing, for mounting on  
door

VBD2

## Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VBD
Device Application	Preventive maintenance
Product Type	Switch disconnecter

## Complementary

Device Composition	Handle Switch
Mounting Support	Handle: door Switch: door
Mounting Method	Hole with 22.5 mm for handle
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Ue] Iec Rated Operational Voltage	690 V AC 50/60 Hz
Iec Rated Operational Power In W	11 kW at 690 V (AC-3) 15 kW at 690 V (AC-23A) 11 kW at 400...415 V (AC-3) 15 kW at 500 V (AC-3) 18.5 kW at 500 V (AC-23A) 5.5 kW at 230...240 V (AC-3) 7.5 kW at 230...240 V (AC-23A) 15 kW at 400...415 V (AC-23A)
[Ie] Rated Operational Current	29 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	40 A
[Ithe] Conventional Enclosed Thermal Current	32 A
Making Capacity ( I Rms)	400 A at 400 V AC-21A 400 A at 400 V AC-22A 400 A at 400 V AC-23A
Breaking Capacity	320 A at 400 V (AC-21A) 320 A at 400 V (AC-22A) 320 A at 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 kA at 400 V - associated fuse 50 A aM 10 kA at 400 V - associated fuse 50 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA at 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	480 A at 400 V duration: 1 s

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>[Uimp] Rated Impulse Withstand Voltage</b>	8 kV
<b>Suitability For Isolation</b>	Yes
<b>Network Type</b>	DC AC
<b>Intermittent Duty Class</b>	30
<b>Control Type</b>	Rotary handle
<b>Rotary Handle Mounting Style</b>	Direct
<b>Handle Color</b>	Black
<b>Handle Front Plate Color</b>	Black
<b>Rotary Handle Padlocking</b>	1 to 3 padlocks 4...8 mm
<b>Marking</b>	0 - 1
<b>Mechanical Durability</b>	100000 cycles
<b>Electrical Durability</b>	100000 cycles AC-21 30000 cycles DC-1...5
<b>Iec Terminal Connection</b>	Power circuit: screw clamp terminals10 mm² - solid Power circuit: screw clamp terminals6 mm² - flexible - with cable end
<b>Tightening Torque</b>	Power circuit: 2.1 N.m - on screw clamp terminals
<b>Base Dimension</b>	60 x 60 mm
<b>Height</b>	74 mm
<b>Width</b>	60 mm
<b>Product Weight</b>	0.215 kg

## Environment

<b>Standards</b>	IEC 60947-3
<b>Product Certifications</b>	CSA CCC GL UL UKCA
<b>Degree Of Protection</b>	IP20 conforming to IEC 60529 IP65
<b>Protective Treatment</b>	TC
<b>Mechanical Robustness</b>	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
<b>Ambient Air Temperature For Operation</b>	-20...50 °C
<b>Fire Resistance</b>	960 °C conforming to IEC 60695-2-1
<b>Compatibility Code</b>	Main switch disconnecter

## Packing Units

<b>Unit Type Of Package 1</b>	PCE
<b>Number Of Units In Package 1</b>	1
<b>Package 1 Height</b>	8.0 cm
<b>Package 1 Width</b>	8.5 cm
<b>Package 1 Length</b>	12.0 cm
<b>Package 1 Weight</b>	221.0 g

Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	5.825 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>