

# Product data sheet

Specifications



## Unica - rocker switch - 2-way - 10 AX 250 VAC - 1 m - ivory

MGU3.103T.25

 **Discontinued on:** Jun 15, 2023

 **Discontinued**

### Main

Range Of Product	Unica
Aesthetic Name	Unica (standard aesthetic)
Product Or Component Type	Switch
Device Presentation	Mechanism
Technology Type	Electromechanical
Switch Function	1-pole 2-way
Number Of Rocker	1
Device Application	Light control
Provided Equipment	Internal power connection
Colour Tint	Ivory

### Complementary

Rated Current	10 AX
[Ue] Rated Operational Voltage	250 V
Network Type	AC
Network Frequency	50/60 Hz
Electrical Durability	10000 cycles
Insulation Resistance	> 5 MOhm at 500 V
Dielectric Strength	2000 V
Minimum Load Breaking Capacity	200 operations 1.25 In and 1.1 Un, cos phi = 0.3
Opening Distance	> 3 mm
Actuator	Rocker
Number Of Modules	1 module
Connections - Terminals	Screw terminals
Cable Cross Section	0...2.5 mm² rigid cable 0...2.5 mm² flexible cable
Material	ASA + PC: mechanism cover
Fixing Mode	Clip-in
Width	22.5 mm
Height	45 mm
Depth	34 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Embedding Depth	22 mm
Net Weight	0.0211 kg
Ambient Air Temperature For Operation	25...35 °C
Ambient Air Temperature For Storage	0...50 °C
Standards	EN 60669-1 EMC directive LV directive

## Environment

Ip Degree Of Protection	IP20
Ik Degree Of Protection	IK01
Environmental Characteristic	Window-cleaning fluid Alcohol Oil UV resistant Bleach Petrol Liquid soap Acetone

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.4 cm
Package 1 Width	2.3 cm
Package 1 Length	4.7 cm
Package 1 Weight	21.0 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	10
Package 2 Height	4.4 cm
Package 2 Width	13.6 cm
Package 2 Length	33.5 cm
Package 2 Weight	210.0 g

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations