


Product data sheet

Specifications



Actassi - traditional link with metallic splitter -LC/LC- OM3- 2 mm- Euroclass C

VDILL031K1K2

⚠ Discontinued on: Feb 10, 2021

⚠ Discontinued

Main

Range	Actassi
Product Or Component Type	Traditional link
Colour	Sheath: aqua LC connector: aqua
Type Of Packing	50...320 m cable drum

Complementary

Product Destination	empty fibre optic patch panel
Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.3 dB 850 nm
Minimum Return Loss	20 dB 850 nm
Fibre Performance	OM3
Optic Fiber Diameter	2 mm
Sheath Type	Metallic cylinder
Condition Of Use	Indoor
Cable Outer Diameter	3.8 mm
Material	Plastic: LC connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	Fibre performance: ITU G.651 Fibre performance: IEC 60793-2-10 Type A1a.2 Cable specification: IEC 60794-2 Cable test procedure: IEC 60794-1-2 Flame retardance: IEC 60332-1 IEC 60754-1 Acidity of combustion gases: IEC 60754-2 Smoke generation: IEC 61034 LC connector: IEC 61754-20 Performance: ISO/IEC 11801:2011 Ed.2.2 Cabling: ISO/IEC 24764 Fibre cabling test: ISO/IEC 14763-3 TIA/EIA-568-C.3 ANSI/TIA-942 10Gbase-SR: IEEE 802.3ae
------------------	--