

Product data sheet

Specifications



PowerPact multistandard - J-Frame - 250 A - 100 KA - Micrologic 3.0 trip unit

NJJF36250U31XTW

Main

Range Of Product	PowerPact multistandard
Range	PowerPact
Product Name	J-Frame
Device Short Name	J-Frame
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Poles Description	3P
Control Type	Toggle
Mounting Mode	Unit mount
Mounting Support	Backplate DIN rail Flush
Electrical Connection	Terminal nut, line side Terminal nut, load side
[In] Rated Current	250 A at 40 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489
Breaking Capacity Code	JJ
Suitability For Isolation	Yes
Utilisation Category	Category A
Mechanical Durability	5000 cycles
Electrical Durability	1000 cycles
Connection Pitch	45 mm
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Trip Unit Name	MicroLogic 3.0
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LI

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Trip Unit Rating	250 A
Thermal Memory	20 mn
Display Type	3 LEDs
Breaking Capacity	Icu: 100 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 65 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 65 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 25 kA at 500/525 V - AC conforming to IEC 947-2 100 kA at 240 V - AC conforming to UL 489 65 kA at 480 V - AC conforming to UL 489 25 kA at 600 V - AC conforming to UL 489
[Ics] Rated Service Breaking Capacity	Ics: 100 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 65 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 65 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 25 kA at 500/525 V - AC conforming to IEC 947-2
Long Time Pick-Up Adjustment Type Ir	Adjustable 9 settings
Long Time Pick-Up Adjustment Range	0.28...1 x In
[Tr] Long-Time Delay Adjustment Range	1 s 4 s 0.5 s 2 s 8 s 16 s
Instantaneous Pick-Up Adjustment Type Ii	Adjustable 9 settings
Instantaneous Pick-Up Adjustment Range	1.5...15 x In
Overvoltage Category	II
Provision For Padlocking	Non padlockable
Height	191 mm
Width	104 mm
Depth	86 mm
Standards	NMX J-266 NEMA AB1 CSA C22.2 No 5 IEC 60947-2 W-C-375B/GEN UL 489
Product Certifications	CE CCC
Net Weight	2.4 kg

Environment

Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1 3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	40 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.500 cm

Package 1 Width	19.000 cm
Package 1 Length	22.000 cm
Package 1 Weight	2.327 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	14.596 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	24
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	70.384 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov