

Product data sheet

Specifications



Circuit breaker, PowerPacT L, 400A, 3 pole, 600VAC, 18kA, busbar, MicroLogic 3.0, multistandard, metric terminal nut

NLGF36400U31XTW

Main

Range Of Product	PowerPact multistandard
Range	PowerPact
Product Name	L-Frame
Device Short Name	L-Frame
Product Or Component Type	Circuit breaker
Device Application	Distribution

Complementary

Poles Description	3P
Control Type	Toggle
Mounting Mode	Unit mount
Mounting Support	Flush DIN rail Backplate
Electrical Connection	Terminal nut, line side Terminal nut, load side
[In] Rated Current	400 A at 40 °C
[Ui] Rated Insulation Voltage	750 V AC 50/60 Hz conforming to IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	8 kV conforming to IEC 60947-2
[Ue] Rated Operational Voltage	525 V AC 50/60 Hz conforming to IEC 60947-2 690 V AC 50/60 Hz conforming to IEC 947-2 600 V AC 50/60 Hz conforming to UL 489
Breaking Capacity Code	LG
Suitability For Isolation	Yes
Utilisation Category	Category A
Mechanical Durability	5000 cycles
Electrical Durability	1000 cycles
Connection Pitch	45 mm
Local Signalling	ON/OFF indication
Contact Position Indicator	Yes
Trip Unit Name	MicroLogic 3.0
Trip Unit Technology	Electronic
Trip Unit Protection Functions	LI

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Trip Unit Rating	400 A
Thermal Memory	20 mn
Display Type	3 LEDs
Breaking Capacity	Icu: 65 kA at 220/240 V - AC conforming to IEC 947-2 Icu: 35 kA at 380/415 V - AC conforming to IEC 947-2 Icu: 35 kA at 440/480 V - AC conforming to IEC 947-2 Icu: 18 kA at 500/525 V - AC conforming to IEC 947-2 65 kA at 240 V - AC conforming to UL 489 35 kA at 480 V - AC conforming to UL 489 18 kA at 600 V - AC conforming to UL 489
[Ics] Rated Service Breaking Capacity	Ics: 65 kA at 220/240 V - AC conforming to IEC 947-2 Ics: 35 kA at 380/415 V - AC conforming to IEC 947-2 Ics: 35 kA at 440/480 V - AC conforming to IEC 947-2 Ics: 18 kA at 500/525 V - AC conforming to IEC 947-2
Long Time Pick-Up Adjustment Type Ir	Adjustable 9 settings
Long Time Pick-Up Adjustment Range	0.31...1 x In
[Tr] Long-Time Delay Adjustment Range	2 s 4 s 0.5 s 16 s 8 s 1 s
Instantaneous Pick-Up Adjustment Type Ii	Adjustable 9 settings
Instantaneous Pick-Up Adjustment Range	1.5...15 x In
Overvoltage Category	II
Provision For Padlocking	Non padlockable
Height	340 mm
Width	140 mm
Depth	110 mm
Standards	NMX J-266 NEMA AB1 IEC 60947-2 UL 489 W-C-375B/GEN CSA C22.2 No 5
Product Certifications	CCC CE
Net Weight	6 kg

Environment

Ip Degree Of Protection	IP40 conforming to IEC 60529
Ik Degree Of Protection	IK07 conforming to IEC 62262
Pollution Degree	3 conforming to IEC 60947-1 3 conforming to IEC 60664-1
Ambient Air Temperature For Operation	40 °C
Ambient Air Temperature For Storage	-50...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	25.6 cm

Package 1 Width	28.0 cm
Package 1 Length	51.1 cm
Package 1 Weight	6.664 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	37.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	51.984 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California Proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov