

Product data sheet

Specifications



ClimaSys indoor slim cooling unit block stainless steel - 3200W at 230 V - UL

NSYCUSX3K2UL

! To be discontinued

! To be discontinued on: Dec 31, 2024

! To be end-of-service on: Dec 31, 2026

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Slim cooling unit block
Mounting Type	Door of enclosure
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	1200 W
Cooling Power	10919 Btu/h 50/60 Hz L35-L35 8530 Btu/h 50/60 Hz L35-L50

Complementary

Height	1696 mm
Width	495 mm
Depth	235 mm
[In] Rated Current	10.5 A
Inrush Current	37 A
Power Consumption In W	1720 W at 50/60 Hz, L35-L35 2000 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	1.9
Control Type	Electronic controller
Temperature Setting Range	20...50 °C
Ambient Air Temperature For Operation	50 °C maximum: 20...46 °C inside the enclosure: 20...50 °C outside the enclosure:
Noise Level	69 dB conforming to EN/ISO 3746
Pressure	28 bar
Flow Rate	Internal circuit: 1450 m3/h at 50/60 Hz External circuit: 1450 m3/h at 50/60 Hz
Net Weight	78 kg
Cooling Gas Type	R134a (0.85 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 16 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	UL
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.5 cm
Package 1 Width	49.5 cm
Package 1 Length	169.6 cm
Package 1 Weight	81.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	2
Package 2 Height	206.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	218.8 kg

Sustainability





Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		REACH Declaration
Eu Rohs Directive		Compliant EU RoHS Declaration
China Rohs Regulation		China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins