

Product data sheet

Specifications



Connected dimmer, Exxact, Wiser by SE, rotary, universal, LED, white

WDE002334

 **Discontinued on:** Jul 14, 2021

 **Discontinued**

Main

Range	Exxact
Product Or Component Type	Connected dimmer
Colour Tint	White (RAL 9003)

Complementary

Concentrator Compatibility	Wiser hub generation 1
Mobile App Name	Wiser by SE
Device Presentation	Mechanism with fixing frame
Device Mounting	Flush
Device Application	Light control
Dimmer Type	Universal
Dimmer Control	Rotary push type
Fixing Mode	By screws
Rated Current	10 A
[Ue] Rated Operational Voltage	230 V
Network Type	AC
Network Frequency	50 Hz
Standby Consumption	Max. 0.4 W
Surface Finish	Glossy
Load Type	Incandescent lamp: 14...200 W at 230 V AC Halogen lamp: 14...150 W at 230 V AC LV halogen lamps: 14...150 VA at 12 V AC (wound transformer) LED lamp: 7...100 VA at 230 V AC (RC LED mode) LED lamp: 7...20 VA at 230 V AC (RL LED mode) LV halogen lamps: 14...150 VA at 12 V AC (electronic transformer)
Protection Type	Overheating protection Automatic overload protection Short-circuit protection
Local Signalling	Programming indication: 1 LED (green/red)
Time Delay Range	1 s...24 h (overtravel)
Communication Network Type	Wireless Zigbee (2.4 GHz), 2.5 mW at < 50 m
Ambient Air Temperature For Storage	5...40 °C
Ambient Air Temperature For Operation	5...40 °C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Screw terminals
Shape Of Screw Head	Pozidriv No 1 and combi
Tightening Torque	0.5 N.m
Clamping Connection Capacity	1.5...2.5 mm² for solid cable(s) 1.5...2.5 mm² for solid stranded cable(s)
Wire Stripping Length	6 mm
Material	ABS (acrylonitrile butadiene-styrene)
Height	71 mm
Width	71 mm
Depth	49 mm
Embedding Depth	27 mm
Net Weight	0.082 kg
Product Certifications	NEMKO CE FIMKO SEMKO

Environment

Ip Degree Of Protection	IP20 IP21 with marking on visual parts
Ik Degree Of Protection	IK02
Standards	EN 301-489-17 EN 60730-2-7 EN 300-328 EN 60669-2-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.900 cm
Package 1 Width	7.100 cm
Package 1 Length	7.100 cm
Package 1 Weight	123.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	36
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.363 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	576
Package 3 Height	115.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	78.336 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information