

Product data sheet

Specifications



ClimaSys standard cooling unit side of enclosure - 820W at 230 V

NSYCUX800

⚠ To be discontinued on: Dec 31, 2024

⚠ To be end-of-service on: Dec 31, 2026

⚠ To be discontinued

Main

Range	ClimaSys
Product Name	CU
Product Or Component Type	Cooling unit
Mounting Type	Side
Installation	Indoor side
Product Destination	For enclosure
Mounting Mode	By screws
Supply Voltage	230 V AC at 50/60 Hz, 1 phase
Rated Power	820 W
Cooling Power	820 W 50/60 Hz L35-L35 680 W 50/60 Hz L35-L50

Complementary

Height	783 mm
Width	348 mm
Depth	215 mm
[In] Rated Current	2.6 A
Inrush Current	10.8 A
Power Consumption In W	440 W at 50/60 Hz, L35-L35 490 W at 50/60 Hz, L35-L50
Energy Efficiency Ratio	1.9
Control Type	Electronic controller
Temperature Setting Range	20...55 °C at 50 Hz 20...50 °C at 60 Hz
Ambient Air Temperature For Operation	20...46 °C inside the enclosure: 55 °C maximum: 20...55 °C at 50 Hz outside the enclosure: 20...50 °C at 60 Hz outside the enclosure:
Noise Level	65 dB conforming to EN/ISO 3746
Pressure	25 bar
Flow Rate	Internal circuit: 330 m3/h at 50/60 Hz External circuit: 570 m3/h at 50/60 Hz
Net Weight	27 kg
Cooling Gas Type	R134a (0.23 kg)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Type Of Filter	Optional external circuit filter
Protection Type	Thermal protection: T 6 A Short-circuit protection (magnetic):
Material	Stainless steel
Colour	Grey (RAL 7035)

Environment

Product Certifications	CE
Directives	2004/108/EC - electromagnetic compatibility 2006/42/EC - machinery 2006/95/EC - low voltage directive
Standards	EN/ISO 12100 EN 60335-1 EN 60335-2-40 EN 378 EN 60204-1
Ip Degree Of Protection	IP55 conforming to IEC 60529 (on the internal circuit) IP34 conforming to IEC 60529 (on the external circuit)

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	21.5 cm
Package 1 Width	34.8 cm
Package 1 Length	78.3 cm
Package 1 Weight	27.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	6
Package 2 Height	100.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	176.2 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information