


Product data sheet

Specifications



One entry cable gland plate,
PanelSeT SFN, Spacial SF, for
electrical enclosure W1600
D500mm, fixed by clips

NSYEC1651

Main

Range	Spacial
Product Or Component Type	Cable gland plate
Accessory / Separate Part Category	Cable management accessory
Application	Multi-purpose
Range Compatibility	Spacial Spacial SF
Mounting Location	Enclosure bottom
Cable Gland Type	Standard
Cable Entry	1 entry
Device Composition	fixing elements 1 plate self extinguishing polyurethane adhesive gasket with cross-section of 15 x 25 mm
Quantity Per Set	Set of 1
Material	Galvanised steel

Complementary

Height	30 mm
Width	Nominal: 1600 mm Useful: 1416 mm
Depth	500 mm nominal:
Thickness	1.5 mm

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	25.0 cm
Package 1 Length	71.5 cm
Package 1 Weight	8.0 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	30
Package 2 Height	29.0 cm
Package 2 Width	80.0 cm
Package 2 Length	120.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Weight	250.0 kg
------------------	----------

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations