

Product data sheet

Specifications

Cost-effective LED Lamps - 120/230 V AC - 10W



NSYLAMT5LD2

Main

Range Of Product	Lighting and power sockets
Accessory / Separate Part Category	Lighting accessory
Product Or Component Type	Lamp
Device Application	Multi-purpose
Device Composition	1 lamp 1 fixing elements 2 cable
Power Factor	0.9

Complementary

Outlet Standard Deviation	Without socket
Rated Lamp Wattage	10 W
[Ue] Rated Operational Voltage	120/230 V AC 50/60 Hz
Bulb Base	Integral LED
Bulb Type	LED
Control Type	Built-it switch
Luminous Flux	1100 lm
Colour Temperature	4000 K
Service Life In Hours	25000 h
Electrical Connection	Cable quick connector 3 m supplied Cable quick connector 1 m supplied
Mounting Support	Cross rails Metal parts
Fixing Mode	Screws Magnetic fixing
Range Compatibility	Spacial Thalassa
Length	560 mm
Height	30.5 mm
Colour	Aluminium

Environment

Ip Degree Of Protection	IP20 conforming to IEC 60529
Electrical Insulation Class	Class I

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 60598
Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-16...65 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.500 cm
Package 1 Width	6.000 cm
Package 1 Length	60.000 cm
Package 1 Weight	639.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	27.000 cm
Package 2 Width	32.000 cm
Package 2 Length	61.500 cm
Package 2 Weight	13.485 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	160
Package 3 Height	90.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	114.240 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information