

# Product data sheet

Specifications

## Pneumatic door retainer, PanelSeT SFN, Spacial SF, 120° opening



NSYSFNDR

### Main

Range	Spacial
Product Or Component Type	Door retainer
Application	Multi-purpose
Nominal Dimensions Of The Housing	-
Mounting Location	Door and enclosure
Range Compatibility	Spacial SF enclosure
Device Composition	Fixing elements 1 x door stop
Quantity Per Set	Set of 1

### Complementary

Fixing Mode	By fixing element - on front frame of enclosure location
Operating Angle	120 °
Opening Mechanism	Pneumatic

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	2.6 cm
Package 1 Length	37.5 cm
Package 1 Weight	327.5 g

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations