

Product data sheet

Specifications



set of 4 Spacial SM M12 lifting eyebolt - galvanized cast steel

NSYSMEB

Main

Area	Spacial
Category	Lifting accessory
Product Or Component Type	Lifting bracket Lifting eye
Application	Multi-purpose
Mounting Location	Enclosure top
Range Compatibility	Spacial Spacial SF Spacial Spacial SM
Device Composition	4 eyebolt 4 fixing nuts
Quantity Per Set	Set of 1

Complementary

Material	Cast steel
Surface Finish	Galvanized
Fixing Mode	Screwed
Permanent Permissible Load	340 kg for 1 eyebolt vertical direction
Height	61.5 mm
Width	54 mm
Depth	26 mm
Diameter	29 mm
Iso Thread	M12

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.0 cm
Package 1 Width	9.0 cm
Package 1 Length	14.5 cm
Package 1 Weight	1.058 kg
Unit Type Of Package 2	PAM
Number Of Units In Package 2	240
Package 2 Height	45.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	100.0 cm
Package 2 Length	120.0 cm
Package 2 Weight	277.0 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations