


# Product data sheet

Specifications



Terminal block, Linergy TR, push-in type, 2 points, 4mm<sup>2</sup>, feed through, grounded, green-yellow, set of 50

NSYTRP42PE

## Main

Range	Linerger
Product Name	Linerger TR
Product Or Component Type	Terminal block
Device Short Name	TRP
Terminal Block Type	Protective earth
Terminal Block Level	1
Mounting Mode	Clip-on
Nominal Cross Section	4 mm <sup>2</sup>
Length	56 mm
Colour	Green-yellow
Quantity Per Set	Set of 50

## Complementary

Width	6.2 mm
Height	36.5 mm
Connections - Terminals	1 x push-in: upstream 1 x push-in: downstream
Number Of Connections	2
Connection Position	Top
Number Of Measurement Input	2
Cable Cross Section	0.08...6 mm <sup>2</sup> , solid 0.2...4 mm <sup>2</sup> , flexible with cable end 0.08...4 mm <sup>2</sup> , flexible without cable end
Wire Stripping Length	12 mm
Tool Type	Disconnection: flat screwdriver Connection: without tool
Material	Polyamide 6/6: insulating case
Dielectric Loss	0.01 at 1 MHz conforming to IEC 60250 0.01 at 1 MHz conforming to VDE 0303-T4
Dielectric Constant	3.7 at 1 MHz
Resistivity	10000 MΩ.m conforming to IEC 60093 10000 MΩ.m conforming to VDE 0303-T30
Surface Resistance	1000 GΩ conforming to IEC 60093 1000 GΩ conforming to VDE 0303-T30

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Creep Resistance	500 CTI (> 400 kB) conforming to IEC 60093 500 CTI (> 400 kB) conforming to VDE 0303-T30
Flame Retardance	V0, thickness0.8 mm conforming to UL 94
Net Weight	12.5 g
Range Compatibility	Prisma G Prisma P Prisma PH Prisma Pack Spacial Kaedra Pragma TeSys
Product Compatibility	Spacial enclosures

## Environment

Product Certifications	IEC-Ex CSA EAC ATEX cURus GL LR
Dielectric Strength	1000 V conforming to IEC 60243-1
Ambient Air Temperature For Operation	-40...130 °C conforming to IEC 60216-1 -40...130 °C conforming to VDE 0304-T21

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.81 cm
Package 1 Width	1.02 cm
Package 1 Length	5.84 cm
Package 1 Weight	0.01 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	50
Package 2 Height	4.7 cm
Package 2 Width	6.8 cm
Package 2 Length	32 cm
Package 2 Weight	529 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	200
Package 3 Height	15 cm
Package 3 Width	15 cm
Package 3 Length	40 cm
Package 3 Weight	2.318 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations