

# Product data sheet

Specifications



Empty control station, Harmony  
XALD, XALK, plastic, yellow, 5 cut-  
outs, unmarked

XALK05

## Main

|                             |  |
|-----------------------------|--|
| Range Of Product            | Harmony XALK   |
| Product Or Component Type   | Empty control station  |
| Device Short Name           | XALK   |
| Product Destination         | For XB5 Ø 22 mm control and signalling units   |
| Control Station Application | Emergency stop function<br>Emergency switching off function  |
| Number Of Cut-Out           | 5 cut-outs   |
| Colour Of Base Of Enclosure | Light grey (RAL 7035)  |
| Colour Of Cover             | Yellow (RAL 1021)  |
| Material                    | Polycarbonate  |
| Cable Entry                 | 2 knock-outs for cable entry, clamping capacity: 14 mm<br>2 knock-outs for Pg 13 cable gland and ISO M20, clamping capacity: 12 mm |
| Ip Degree Of Protection     | IP66 conforming to IEC 60529<br>IP67<br>IP69<br>IP69K  |

## Complementary

|                                    |                                       |
|------------------------------------|---------------------------------------|
| Assembly Style                     | For customer assembly                 |
| Number Of Horizontal Rows          | 1                                     |
| Number Of Vertical Rows            | 5                                     |
| Net Weight                         | 0.322 kg                              |
| Resistance To High Pressure Washer | 7000000 Pa at 55 °C, distance : 0.1 m |
| Mounting Of Block                  | Rear mounting<br>Front mounting       |
| Main Group                         | 5 cut-outs                            |
| Group Of Product                   | Standard yellow                       |

## Environment

|                                       |                                  |
|---------------------------------------|----------------------------------|
| Protective Treatment                  | TH                               |
| Ambient Air Temperature For Storage   | -40...70 °C                      |
| Ambient Air Temperature For Operation | -40...70 °C                      |
| Overvoltage Category                  | Class II conforming to IEC 60536 |
| Nema Degree Of Protection             | NEMA 13<br>NEMA 4X               |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                |   |
|--------------------------------|---|
| <b>Ik Degree Of Protection</b> | IK03 conforming to EN 50102   |
| <b>Standards</b>               | UL 508<br>EN/IEC 60947-5-1<br>EN/IEC 60947-1<br>EN/IEC 60947-5-4<br>JIS C8201-5-1<br>EN/IEC 60947-5-5<br>CSA C22.2 No 14<br>JIS C8201-1 |

## Packing Units

|                                     |         |
|-------------------------------------|---------|
| <b>Unit Type Of Package 1</b>       | PCE     |
| <b>Number Of Units In Package 1</b> | 1       |
| <b>Package 1 Height</b>             | 19.7 cm |
| <b>Package 1 Width</b>              | 7.0 cm  |
| <b>Package 1 Length</b>             | 7.6 cm  |
| <b>Package 1 Weight</b>             | 312.0 g |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| <b>Warranty</b> | 18 months |
|-----------------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free


✓ Rohs Exemption Information   Yes

## Certifications & Standards

|                          |   |
|--------------------------|---|
| Reach Regulation         | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
| China Rohs Regulation    | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile      | <a href="#">End of Life Information</a>   |

Dimensions Drawings

Dimensions



- (1) 2 knock-outs for Pg 13.5 cable gland, maximum capacity 12 mm/0.47 in.  
(2) Knock-out for cable entry, maximum capacity 14 mm/0.55 in.

| Control station fitted with:                              | c in mm | c in in. |
|---|---------|----------|
| Flush pushbutton  | 62      | 2.44     |
| Pilot light   | 64      | 2.52     |
| Illuminated pushbutton                                    | 65.5    | 2.58     |
| Projecting pushbutton                                     | 66      | 2.60     |
| Selector switch   | 80      | 3.15     |
| Mushroom head pushbutton                                  | 91.5    | 3.58     |
| Latching mushroom head Emergency stop pushbutton with key | 115     | 4.53     |
| Key switch  | 105.5   | 4.15     |