

Product data sheet

Specifications



Exiway Power Control Nano - central battery system - 4 Main cct 80 lum (Max)

OVA18049

Main

| | |
|---------------------------|------------------------------|
| Range | Exiway |
| Product Name | Exiway Power Control |
| Device Short Name | Exiway Power Control Nano |
| Product Or Component Type | Central battery system |
| Number Of Circuits | 4 |
| Number Of Light Blocks | 80 |
| Device Composition | 2 main circuit module |
| Supply | Maintained Non-maintained |

Complementary

| | |
|---------------------------------------|---|
| [Us] Rated Supply Voltage | 230 V 50 Hz |
| Poles Description | 1P |
| Output Voltage | 230 V AC 216 V DC |
| Rated Power In W | 1500 W 1 h 6.95 A 500 W 3 h 2.32 A 300 W 8 h 1.39 A |
| Rated Power In Va | 2000 VA |
| Number Of Batteries | 18 12 V 17 Ah |
| Display Type | LCD display |
| Communication Network Type | Ethernet TCP/IP |
| Communication Port Support | RS485 RS232 |
| Communication Port Protocol | Modbus |
| Web Services | Web server |
| Language | Multi-language |
| Cover Type | Lockable cover to be ordered separately |
| Battery Type | Lead-acid battery |
| Charging Time | 12 h 80 % autonomy |
| Provided Equipment | Light switch query module MMO internal I/O module internal Battery temperature sensor Critical circuit interface module internal |
| Ambient Air Temperature For Operation | 0...35 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------|-------------|
| Material | Sheet steel |
| Maximum Power | 1500 W |

Environment

| | |
|-----------------------------|--|
| Colour | Grey |
| Colour Code | RAL 7035 |
| Ip Degree Of Protection | IP20 |
| Mounting Mode | Wall-mounted Floor-standing |
| Electrical Insulation Class | Class I |
| Standards | EN 61547 EN 50171 DIN VDE 0100-718 EN 55015 DIN VDE 0108-100 EN 61000-3-2 EN 50172 IEC 60364-5-56 EN 61000-3-3 EN 50272-2 |
| Height | 1100 mm |
| Width | 500 mm |
| Depth | 230 mm |
| Net Weight | 140 kg |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 50.0 cm |
| Package 1 Width | 110.0 cm |
| Package 1 Length | 23.0 cm |
| Package 1 Weight | 165.5 kg |

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation