


Product data sheet

Specifications



Evx Ferro - con kit - adressable - 10 VA - 6.0 V - 4 Ah

OVA34214E

 **Discontinued on:** Dec 31, 2015

 **Discontinued**

Main

Range	Evx
Aesthetic Name	Evx Ferro
Product Or Component Type	Conversion kit
Function	Addressable
Wiring Device Additional Information	Can be inhibited with rest mode via Dardo Plus control unit

Complementary

[Ue] Rated Operational Voltage	230 V 50 Hz
Rated Power In Va	10 VA
Connections - Terminals	Screw terminals
Battery Capacity	4 Ah 6 V Ni-Cd (Nickel-Cadmium) in line
Charging Time	24 h

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Emergency Luminous Flux	17 % of nominal flux during 1 h 54 W G5 fluorescent FHO T5 20 % of nominal flux during 1 h 30 38 W GR10q fluorescent GE 20 % of nominal flux during 1 h 39 W G5 fluorescent FHO T5 30 % of nominal flux during 1 h 30 24 W G5 fluorescent FHO T5 40 % of nominal flux during 1 h 30 21 W G5 fluorescent FHE T5 45 % of nominal flux during 1 h 30 14 W G5 fluorescent FHE T5 15 % of nominal flux during 1 h 55 W GR10q 15 % of nominal flux during 1 h 58 W G13 16 % of nominal flux during 1 h 30 36 W 2G10 18 % of nominal flux during 1 h 30 36 W G13 18 % of nominal flux during 1 h 30 40 W G10q 20 % of nominal flux during 1 h 30 32 W G10q 20 % of nominal flux during 1 h 30 36 W 2G11 22 % of nominal flux during 1 h 40 W 2GX13 22 % of nominal flux during 2 h 18 W G13 25 % of nominal flux during 1 h 2 x 18 W G13 25 % of nominal flux during 1 h 30 24 W 2G11 25 % of nominal flux during 2 h 24 W 2G10 25 % of nominal flux during 2 h 30 22 W G10q 26 % of nominal flux during 1 h 30 26 W G24q 26 % of nominal flux during 1 h 40 W 2G11 28 % of nominal flux during 1 h 30 28 W GR10q 28 % of nominal flux during 2 h 22 W 2GX13 28 % of nominal flux during 2 h 30 18 W 2G10 28 % of nominal flux during 2 h 30 18 W 2G11 30 % of nominal flux during 1 h 30 26 W Gx24q 30 % of nominal flux during 1 h 32 W Gx24q 35 % of nominal flux during 2 h 18 W G24q 37 % of nominal flux during 2 h 18 W Gx24q 38 % of nominal flux during 2 h 30 13 W G5 38 % of nominal flux during 3 h 30 8 W G5 40 % of nominal flux during 1 h 30 16 W GR10q 40 % of nominal flux during 3 h 30 10 W G24q 45 % of nominal flux during 1 h 30 2 x 8 W G5 45 % of nominal flux during 2 h 13 W G24q 45 % of nominal flux during 2 h 13 W Gx24q 50 % of nominal flux during 3 h 30 9 W 2G7 60 % of nominal flux during 3 h 30 7 W 2G7 70 % of nominal flux during 4 h 5 W 2G7 8 % of nominal flux during 1 h 55 W 2G11
Bulb Type	Indicator LED
Ballast Type	Electromagnetic ballast
Electrical Insulation Class	Class II
Height	Battery: 35 mm Circuit: 40 mm
Width	Circuit: 197 mm
Depth	Circuit: 32 mm Battery: 39 mm
Distance Between Centers	Circuit: 180 mm Battery: 330 mm
Net Weight	0.88 kg
Environment	
Fire Resistance	850 °C
Standards	IEC 60695-2-10 EN 61347-2-7
Packing Units	
Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	8 cm

Package 1 Length	34.5 cm
Package 1 Weight	0.871 kg

Contractual warranty

Warranty	18 months
----------	-----------