

Product data sheet

Specifications



Quick Signal - emergency exit sign - standard - maintained - 3 h

OVA38505E

⚠ Discontinued on: May 18, 2021

⚠ Discontinued

Main

Range	Exiway
Product Name	Quick Signal
Product Or Component Type	Emergency exit sign
Device Application	Signalling
Function	Standard
Supply	Maintained
Colour	White
Light Source Colour	White
Provided Equipment	bracket wall/flag installation
Cover Type	Transparent

Complementary

Range Compatibility	TBS remote control
[Ue] Rated Operational Voltage	200...230 V AC/DC 50 Hz
Power Consumption In Va	4.1 VA
Current Consumption	17 mA
Electrical Insulation Class	Class II
Battery Capacity	1.5 Ah at 4.8 V, Ni-Cd (Nickel-Cadmium)
Autonomy	3 h
Charging Time	24 h
Bulb Type	LED 100000 h
Luminous Flux	Maintained mode: 14 lm Emergency condition: 12 lm
Visibility Distance	28 m
Indicator Type	Indicator two sides
Material	Plastic: housing Plastic: cover
Device Mounting	Surface ceiling Hanging ceiling Surface wall Flush false ceiling Flag type bracket wall Flush
Height	235 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	290 mm
Depth	60 mm
Net Weight	0.9 kg

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	0...40 °C
Fire Resistance	850 °C
Standards	IEC 695-2-1 IEC 50-11 EN 60598-2-22 EN 60695-2-10 EN 1838

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

<div><div>✓</div><div>Toxic Heavy Metal Free</div></div>	
<div><div>✓</div><div>Mercury Free</div></div>	
<div><div>✓</div><div>Rohs Exemption Information</div></div>	<div>Yes</div>
<div>Eu Rohs Directive</div>	<div><div>Compliant</div><div>EU RoHS Declaration</div></div>
<div>China Rohs Regulation</div>	<div><div>China RoHS declaration</div><div>Pro-active China RoHS declaration (out of China RoHS legal scope)</div></div>
<div>Circularity Profile</div>	<div>End of Life Information</div>