

Product data sheet

Specifications

battery - 4.8 V - 4 Ah - Ni-Cd - in line



OVA58994

⚠ Discontinued on: Dec 21, 2021

⚠ Discontinued

Main

Range	Exiway
Product Or Component Type	Battery
Device Application	Lighting
Number Of Cells	4
Body Type	Sealed

Complementary

Range Compatibility	Exiway Exiway One emergency light fitting Exiway Exiway Plus emergency light fitting Exiway Exiway Class emergency light fitting
Product Compatibility	Exiway Class Exiway Plus Exiway One
Rated Voltage	4.8 V 4 Ah Ni-Cd (Nickel-Cadmium) battery
Battery Size	KRMT 33/62
Operating Position	In line
Diameter	33 mm
Length	247 mm
Height	37 mm
Width	33 mm
Net Weight	0.52 kg

Environment

Ambient Air Temperature For Operation	-10...50 °C
---------------------------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.5 cm
Package 1 Width	5 cm
Package 1 Length	25 cm
Package 1 Weight	485 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive [Compliant](#)
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)
Pro-active China RoHS declaration (out of China RoHS legal scope)

Environmental Disclosure [Product Environmental Profile](#)