

# Product data sheet

Specifications



## Séquence5 - presence movement detector - 40...300 W - 2 wires - Copper

S800524CS

! Discontinued

! Discontinued on: Jul 26, 2021

! End-of-service on: Aug 19, 2021

### Main

Range	Sequence5
Product Or Component Type	Presence detector
Device Presentation	Complete product
Type Of Packing	Box
Quantity Per Set	1 piece
Sale Per Indivisible Quantity	1
Wiring Device Additional Information	Manual override with push-buttons NC

### Complementary

Device Mounting	Flush
Fixing Mode	By screws
Colour Tint	Copper
Surface Finish	Glossy
Movement Detection Area	10 x 20 m (PIR mounting height 1.2 m)
Presence Detection Area	10 x 18 m (PIR mounting height 1.2 m)
Detection Angle	112°
Selection Modes	A: automatic M: manual
Light Intensity Adjustment	5...1000 lux
Wiring Configuration	2-wire
Time Delay	5 s...20 min
Load Type	230 V AC incandescent lamp 40...350 W 230 V AC halogen lamp 40...350 W
[Ue] Rated Operational Voltage	230 V AC 50 Hz
Protection Type	Fuse protection
Number Of Pin In Parallel	40 W for 1 PIR in parallel 50 W for 2 PIR in parallel 80 W for 3 PIR in parallel
Connected Auxiliaries	Maximum 3 detectors in parallel for a load
Number Of Terminals	2 screw terminals
Shape Of Screw Head	Pozidriv No 1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm² for solid cable(s) 1 x 1.5...2 x 2.5 mm² for stranded cable(s) 1 x 1.5...2 x 2.5 mm² for flexible cable(s)
Wire Stripping Length	8 mm
Material	Metal
Mounting Height	1...1.4 m
Height	80 mm
Width	80 mm
Depth	47 mm
Embedding Depth	43 mm
Net Weight	0.232 kg

## Environment

Ambient Air Temperature For Storage	-5...50 °C
Ambient Air Temperature For Operation	-5...35 °C
Derating Factor	With power derating 5 W per °C above 25 °C
Standards	2006/95/EEC EN 60669-2-1 2004/108/EC EN 61000-6-2
Product Certifications	LCIE: CCA-SE_4179 N NF
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	10 cm
Package 1 Length	12.5 cm
Package 1 Weight	267 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

Eu Rohs Directive

Compliant with Exemptions

China Rohs Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information