

Product data sheet

Specifications



APC Parallel Maintenance Bypass Panel, up to 3 units 30-40kVA, 400V Wallmount

SBPAR30K40H-WP

! Discontinued

! Discontinued on: Jul 5, 2021

! End-of-service on: Oct 18, 2023

Overview

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage 400 V 3 phases

Main Output Voltage 400 V 3 phases

Other Output Voltage 380 V
415 V

Rated Power In Va 120000 VA

Output Connector Type Hard wire 5-wire (3P + N + E) 1

Provided Equipment Installation guide
User manual

Batteries & Runtime

Additional Information Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage

Physical

Height 117.4 cm

Width 56 cm

Depth 21.6 cm

Net Weight 53 kg

Mounting Support Wall

Mounting Preference No preference

Mounting Mode Not rack-mountable

Input

Network Frequency 50 Hz

Conformance

Standards EN 50091-2
EN/IEC 62040-3
EN/IEC 62040-1-1
VFI-SS-111

Environmental

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-15...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...9144.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	129.8 cm
Package 1 Width	70.4 cm
Package 1 Length	33.5 cm
Package 1 Weight	54.885 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Compliant

[EU RoHS Declaration](#)
