

Product data sheet

Specifications



APC Smart-UPS VT Maintenance Bypass Panel 10-20kVA 400V Wallmount

SBPSU10K20HC1M1-WP

Overview

Lead Time	Usually Ships within 4 Weeks
-----------	------------------------------

Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	400 V 3 phases
Number Of Cables	1
Provided Equipment	Installation guide User manual

Physical

Colour	Black
Height	31.5 cm
Width	30.5 cm
Depth	17.5 cm
Net Weight	7.01 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Network Frequency	50 Hz +/- 3 Hz
-------------------	----------------

Conformance

Standards	EN 50091-2 EN/IEC 62040-3 EN/IEC 62040-1-1
-----------	--

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...50000 ft
Ambient Air Temperature For Storage	0...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	44.2 cm
Package 1 Width	25.4 cm
Package 1 Length	38.1 cm
Package 1 Weight	7.73 kg
Number Of Units In Package 3	1

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------