

Product data sheet

Specifications



Cubicle, SM6-24, PM, IAC 12,5kA
1s, 24kV 12,5kA 1s, 630A, CIT, 4
auxiliary contacts 2O/2C

SM61FS20I2PM06CR03

Main

Range Of Product	SM6
Technology Type	Air insulated switchgear
Device Short Name	PM 375
Product Or Component Type	Fuse-switch
Internal Arc Classification	AFL
Internal Arc Protection	12.5 kA 1 s
Rated Frequency (Fr)	50 Hz
Rated Voltage (Ur)	24 kV
Rated Continuous Current (Ir)	630 A
Rated Short-Time Withstand Current (Ik)	12.5 kA rms 1 s
Standards	IEC 62271-100

Complementary

Cable Connection	1 single core 95 mm ² per phase
Cable Entry	Bottom
Bus Rated Current	630 A
Type Of Operator	CIT manual
Mass	130 kg
Width	375 mm
Depth	940 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Ip Degree Of Protection	IP3x
Vibration Resistance	0.5 gn horizontal class 2 0.4 gn vertical class 2
Operating Altitude	<= 1000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	94.0 cm

Package 1 Width	37.5 cm
Package 1 Length	160.0 cm
Package 1 Weight	145.0 kg
