

Product data sheet

Specifications



APC Smart-UPS X, Line Interactive,
1000VA, Rack/tower convertible 2U,
230V, 8x C13 IEC, SmartSlot,
Extended runtime

SMX1000I

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	800 W
Rated Power In Va	1000 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 320 C14
Output Connection Type	8 IEC 320 C13 2 IEC Jumpers
Number Of Rack Unit	2U
Cable Length	1.83 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	CD with software Documentation CD Installation guide Rack mounting brackets Removable support feet Smart UPS signalling RS-232 cable USB cable

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Extended Runtime	0
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	3 h
Number Of Battery Replacement Quantity	1
Overcurrent Protection	60 A
Battery Life	3...5 year(s)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Replacement Battery	APCRBC116 
Battery Charger Power	99 W rated

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Product Web Sub-Family	Extended run
Redundant	No

Physical

Colour	Black
Height	8.9 cm
Width	43.2 cm
Depth	49 cm
Net Weight	22.86 kg
Mounting Preference	Lower
Mounting Mode	Rack-mounted with kit
Two Post Mountable	1
Usb Compatible	No

Input

Input Voltage Limits	151...302 V adjustable 160...286 V
Network Frequency	50/60 Hz +/- 3 Hz auto-sensing

Output

Harmonic Distortion	Less than 5 %
Maximum Configurable Power In Va	1000 VA
Maximum Configurable Power In W	800 W
Ups Type	Line interactive
Wave Type	Sine wave
Output Frequency	50/60 Hz +/- 3 Hz sync to mains

Conformance

Product Certifications	CE RCM VDE EAC
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Acoustic Level	40 dBA
Heat Dissipation	82 Btu/h

Operating Altitude	0...10000 ft
Ambient Air Temperature For Operation	0...45 °C
Ambient Air Temperature For Storage	-15...45 °C
Storage Altitude	0.00...15240.00 m
Relative Humidity	0...95 %
Storage Relative Humidity	0...95 %

Communications & Management

Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes
Free Slots	1
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge Energy Rate	600 J
Noise Suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24.6 cm
Package 1 Width	62 cm
Package 1 Length	58.9 cm
Package 1 Weight	27.32 kg

Contractual warranty

Warranty	3 years repair or replace (excluding battery) and 2 years for battery
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information