

Product data sheet

Specifications



APC Easy UPS On-Line, 1000VA/
800W, Tower, 230V, 3x IEC C13
outlets, Intelligent Card Slot, LCD,
Extended runtime

SRV1KIL

Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	800 W
Rated Power In Va	1000 VA
Input Connection Type	IEC 60320 C14
Output Connection Type	3 IEC 60320 C13
Cable Length	1.50 m
Number Of Cables	1
Provided Equipment	1 IEC 60320 C13 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable 1 battery cable user manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-acid battery
Battery Voltage	36 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4.5 h
Battery Life	3...5 year(s)
Battery Charger Power	175 W rated

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	23.8 cm
Width	29 cm
Depth	40 cm
Net Weight	24 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	No
Mounting Position	Vertical

Input

Input Voltage Limits	110...285 V half load 160...280 V full load
Network Frequency	40...70 Hz auto sensing

Output

Maximum Configurable Power In Va	1000 VA
Maximum Configurable Power In W	800 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic Distortion	3 %
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	88 % (full load)
Additional Information	Configurable for 220 : 230 or 240 nominal output voltage
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

Conformance

Product Certifications	CE UKCA EAC TISI
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA
Heat Dissipation	372 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Free Slots	1
Control Panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge Energy Rate	600 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	2
Package 1 Height	35.5 cm
Package 1 Width	47 cm
Package 1 Length	52.5 cm
Package 1 Weight	26.7 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information