

Product data sheet

Specifications



APC Easy UPS On-Line, 3kVA/
2400W, Rackmount 2U, 230V, 6x
IEC C13 + 1x IEC C19 outlets,
Intelligent Card Slot, LCD, W/ rail kit

SRV3KRIRK

Overview

Presentation	High quality, Double-conversion On-line UPS designed for essential power protection needs even in the most unstable power conditions.
Lead Time	Usually in Stock

Main

Main Input Voltage	230 V
Product Or Component Type	Uninterruptible power supply (UPS)
Other Input Voltage	220 V 240 V
Main Output Voltage	230 V
Other Output Voltage	220 V 240 V
Rated Power In W	2400 W
Rated Power In Va	3000 VA
Input Connection Type	IEC 60320 C20
Output Connection Type	6 IEC 60320 C13 1 IEC 60320 C19
Number Of Rack Unit	2U
Cable Length	1.48 m
Number Of Cables	1
Provided Equipment	1 IEC 60320 C19 to Schuko power cable 1 IEC 60320 C13 to C14 power cable 1 USB cable 1 RS-232 configuration cable 1 rack mounting brackets 1 rack mounting support rails user manual

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	Lead-acid battery
Battery Voltage	72 V
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	4 h

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery Life	3...5 year(s)
Replacement Battery	APCRBCV202 
Battery Charger Power	60 W rated

General

Number Of Power Module Filled Slots	0
Number Of Power Module Free Slots	0
Redundant	No

Physical

Colour	Black (RAL 7010)
Height	8.6 cm
Width	43.7 cm
Depth	63.2 cm
Net Weight	27.6 kg
Mounting Location	Front
Mounting Preference	Lower
Mounting Mode	Rack-mounted
Usb Compatible	Yes
Mounting Position	Horizontal

Input

Input Voltage Limits	110...285 V half load 160...280 V full load
Network Frequency	40...70 Hz auto sensing

Output

Maximum Configurable Power In Va	3000 VA
Maximum Configurable Power In W	2400 W
Output Frequency	50/60 Hz +/- 3 Hz sync to mains
Harmonic Distortion	3 %
Ups Type	Double conversion online
Wave Type	Sine wave
Efficiency	88 % (full load)
Bypass Type	Internal bypass (automatic and manual)
Crest Factor	3 : 1

Conformance

Product Certifications	CE UKCA EAC TISI
------------------------	---------------------------

Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
-----------	--

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3000 m
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...95 % non-condensing
Storage Altitude	0...15000 m
Acoustic Level	50 dBA
Heat Dissipation	910 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Free Slots	1
Control Panel	Multifunction LCD status and control console

Surge Protection and Filtering

Surge Energy Rate	600 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.8 cm
Package 1 Width	79.4 cm
Package 1 Length	57 cm
Package 1 Weight	29 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information