

Product data sheet

Specifications



APC Smart-UPS VT 10kVA 208V w/ 4 Batt Mod., Start-Up 5X8, Int Maint Bypass, Parallel Capable

SUVTP10KF4B4S

! Discontinued

! Discontinued on: Jul 5, 2021

! End-of-service on: Oct 18, 2023

Overview

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage	208 V 3 phases
Other Input Voltage	220 V
Main Output Voltage	120 V 208 V 208 V 3 phases
Other Output Voltage	220 V
Rated Power In W	8000 W
Rated Power In Va	10000 VA
Output Connector Type	Hard wire 5-wire (3P + N + E) 1
Connections - Terminals	1 screw terminals
Provided Equipment	Battery modules ship installed CD with software Network management card Power modules ship installed Smart UPS signalling RS-232 cable User manual Bolt down brackets Installation guide Start up included

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Battery Type	VRLA
Number Of Battery Filled Slots	4
Number Of Battery Free Slots	0
Battery Recharge Time	5 h
Number Of Battery Replacement Quantity	4
Battery Charger Power	1941 W rated
Battery Life	3...5 year(s)
Extended Runtime	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Ups Type	Double conversion online
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	Yes

Physical

Colour	Black
Height	149.9 cm
Width	52.3 cm
Depth	81.3 cm
Net Weight	599.09 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	40...70 Hz
Number Of Input Connectors	1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	165...240 V
Maximum Input Current	27 A
Switching Current Capacity	35 A
Input Power Factor At Full Load	0.98

Output

Maximum Configurable Power In Va	10000 VA
Maximum Configurable Power In W	8000 W
Output Frequency	57...63 Hz for 60 Hz nominal sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised
Wave Type	Sine wave
Harmonic Distortion	Less than 5 % at full load
Maximum Output Current	31 A
Crest Factor	Unlimited
Bypass Type	Built-in maintenance bypass Built-in static bypass
Additional Information	Configurable for 208 and 220V - 3 Phase

Conformance

Product Certifications	cUL listed UL 1778
------------------------	-----------------------

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-50...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	54 dBA
Heat Dissipation	2047 Btu/h
Nema Degree Of Protection	NEMA 1

Communications & Management

Free Slots	0
Preinstalled Device	Network management card 2 with environmental monitoring
Emergency Power Off	Yes

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	164.3 cm
Package 1 Width	106.2 cm
Package 1 Length	65 cm
Package 1 Weight	630 kg

Contractual warranty

Warranty	1 year repair or replace, Start-Up Service
----------	--

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)





Take-back Transparency RoHS/REACH

Resource performance

 Take-Back Program Available

Well-being performance

 Mercury Free

 Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 **WARNING:** This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov