


Product data sheet

Specifications



Safety switch, Telemecanique
Safety switches XCS, plastic
XCSTE, 2 NC, slow break, 1entry
tapped M16, 24 V

XCSTE7312

Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety switch
Component Name	XCSTE
Design	Rectangular
Material	Plastic
Head Type	Key operated turret head
Contacts Type And Composition	2 NC
Contact Operation	Slow-break, simultaneous
Solenoid Contacts Type And Composition	1 NO (slow-break)
Cable Entry	1 entry tapped for M16 x 1.5
Electromagnet Interlocking	Locking on de-energisation and unlocking on energisation of solenoid
[Us] Solenoid Rated Supply Voltage	24 V - 20...10 %
Cable Outer Diameter	7...10 mm
Electrical Connection	Terminal, clamping capacity: 1 x 0.5...2 x 1.5 mm² with or without cable end
Number Of Poles	2
Locking Options Description	With interlocking, locking by solenoid

Complementary

Insulation	Double insulated
Positive Opening	With NC contact
Supply Voltage Type	AC/DC
Supply Frequency	50/60 Hz
Load Factor	1
Power Consumption In Va	10 VA
Mechanical Durability	1000000 cycles
Positive Opening Minimum Force	15 N
Minimum Actuation Speed	0.01 m/s
Maximum Actuation Speed	0.5 m/s
[Ie] Rated Operational Current	0.55 A at 125 V, DC-13, Q300 conforming to IEC 60947-5-1 0.27 A at 250 V, DC-13, Q300 conforming to IEC 60947-5-1 3 A at 120 V, AC-15, B300 conforming to IEC 60947-5-1 1.5 A at 240 V, AC-15, B300 conforming to IEC 60947-5-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Ithe] Conventional Enclosed Thermal Current	6 A
[Uij] Rated Insulation Voltage	300 V conforming to UL 508 500 V conforming to IEC 60947-1 300 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to IEC 60947-5-1
Short-Circuit Protection	10 A cartridge fuse type gG (gl)
Actuator Forcible Withdrawal Rtc	500 N
Maximum Operating Rate	10 cyc/mn for maximum durability
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear
Body Material	PA (polyamide)
Head Material	PA (polyamide)
Depth	33 mm
Height	94 mm
Width	110 mm
Net Weight	0.36 kg

Environment

Standards	ISO 12100 IEC 60947-5-1 UL 508 IEC 60204-1 CSA C22.2 No 14 EN 1088/ISO 14119
Product Certifications	UL CSA
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...60 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	5 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	10 gn for 11 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class II conforming to IEC 61140
Ip Degree Of Protection	IP67 conforming to EN/IEC 60529 and EN/IEC 60947-5-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	11.500 cm
Package 1 Length	11.000 cm
Package 1 Weight	396.000 g

Unit Type Of Package 2	S02
Number Of Units In Package 2	22
Package 2 Height	15.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	9.022 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

California Proposition 65
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov