

Product data sheet

Specifications



Symmetra PX 125kW Scalable to 500kW with Maintenance Bypass and Distribution, No Batteries

SY125K500DR-PDNB

Overview

Presentation	A high-performance, 3-phase, modular, scalable, power protection solution with industry-leading efficiency, capacity, and performance for medium to large data centers and mission critical environments.
Lead Time	Usually Ships within 6 Weeks

Main

Main Input Voltage	480 V 3 phases 400 V 3 phases
Other Input Voltage	415 V
Main Output Voltage	480 V 3 phases 400 V 3 phases
Other Output Voltage	415 V
Rated Power In W	125000 W
Rated Power In Va	125000 VA
Output Connector Type	Hard wire 4-wire (3P + E) 1
Provided Equipment	Assembly service Installation guide Network management card Start-up service User manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Free Slots	0
Extended Runtime	1

General

Bypass Voltage Tolerance	+/- 10 % settable from +/- 4/6/8 and 10 %
Number Of Power Module Free Slots	15
Number Of Power Module Filled Slots	5
Redundant	Yes

Physical

Colour	Black
Height	199.1 cm
Width	220 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Depth	107 cm
Net Weight	1499 kg
Usb Compatible	No

Input

Network Frequency	40...70 Hz auto-sensing
Number Of Input Connectors	1 hard wire 4-wire (3P + E) 1 hard wire 5-wire (3P + N + E)
Input Voltage Limits	408...552 V 480 V
Max Short Time Withstand Current	50 kA
Input Harmonic Distortion	Less than 5 % for full load
Input Protection Type	3-pole circuit breaker
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	0.99

Output

Maximum Configurable Power In W	500000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised 60 Hz sync to mains
Ups Type	Double conversion online
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 2% linear load and < 3% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Bypass Type	Built-in maintenance bypass Built-in static bypass
Efficiency	96 % (in battery operation)
Maximum Configurable Power In Va	500000 VA
Transfer Time	2 ms typical

Conformance

Product Certifications	cUL listed UL listed
Standards	CSA C22.2 No 107.3-05 EN/IEC 62040-1-1 EN/IEC 62040-2 EN/IEC 62040-3 UL 1778 UL 60950-1

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft

Ambient Air Temperature For Storage	-30...70 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	54 dBA
Heat Dissipation	19427 Btu/h
Nema Degree Of Protection	NEMA 1
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	1
Preinstalled Device	Network management card 2 with environmental monitoring, out of band access and Modbus
Control Panel	Touch screen LCD user interface
Emergency Power Off	Optional

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215 cm
Package 1 Width	127 cm
Package 1 Length	187 cm
Package 1 Weight	1686 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient

Resource performance

 Energy Efficient Product

Eu Rohs Directive

Not compliant