

Product data sheet

Specifications



Single stage heavy duty screw limit switch, XR and XF, XR2, 10 C/O, sheet steel enclosure

XR2AB10K80

⚠ Discontinued on: Jan 16, 2023

⚠ Discontinued

Main

Range Of Product	XR and XF
Product Or Component Type	Single-stage heavy duty screw limit switch
Device Short Name	XR2
Product Specific Application	Position control of moving parts of hoisting or materials handling equipment Liquid level control in pumping systems
Material	Sheet steel: enclosure
Type Of Operator	Drive shaft, end fittings with sprocket key and washer
Maximum Revolution Speed	350 rpm of input drive shaft
Theoretical Number Of Turns	80 of input drive shaft
Number Of Poles	1

Complementary

Mechanical Durability	10000000 cycles
Maximum Number Of Turns	6 of threaded shaft
Threaded Shaft Screw Pitch	4 mm
Operating Finger Radius	40 mm
Length Of Developed Helical Travel	4 mm
Differential Snap Over Angle	30 ° contact actuators measured at finger
Repeat Accuracy	0.02 % on the tripping point
Number Of Teeth	16 (pinion A) 16 (pinion C) 59 (pinion B) 59 (pinion D)
Actual Number Of Turns	81.586 (input drive shaft)
Contacts Type And Composition	10 C/O
Contact Operation	Snap action
[Ie] Rated Operational Current	A300, AC-15, Ue = 240 V, Ie = 3 A conforming to EN/IEC 60947-5-1 Q300, DC-13, Ue = 250 V, Ie = 0.27 A conforming to EN/IEC 60947-5-1
[Ithe] Conventional Enclosed Thermal Current	10 A
[Ui] Rated Insulation Voltage	500 V conforming to EN/IEC 60947-1 600 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	6 kV conforming to EN/IEC 60947-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Resistance Across Terminals	25 MOhm
Short-Circuit Protection	10 A cartridge fuse gG
Connections - Terminals	Screw clamp terminals, 2 x 1.5 mm² with or without cable end Screw clamp terminals, 2 x 2.5 mm² without cable end

Electrical Durability

[illegible]

3000000 cycles DC-13 inductive at 110 V, 110 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 inductive at 12 V, 100 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 inductive at 220 V, 95 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 inductive at 24 V, 140 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 inductive at 440 V, 65 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 inductive at 48 V, 130 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 110 V, 95 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 12 V, 100 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 220 V, 80 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 24 V, 120 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 440 V, 45 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

3000000 cycles DC-13 resistive at 48 V, 110 W, operating rate <3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1

Cable Entry	Removable gland plate
Net Weight	15 kg

Environment

Standards	EN/IEC 60947-5-1
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Shock Resistance	50 gn for 11 ms
Vibration Resistance	> 5 gn (f= 10...55 Hz)
Ip Degree Of Protection	IP54 conforming to EN/IEC 60529

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Reach Regulation	REACH Declaration
Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
California Proposition 65	WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov