

Product data sheet

Specifications



250V 1 Gang 13A Switched BS Socket Module, Amber LED

US15_A00

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Product Or Component Type	Socket module
Number Of Gangs	1 gang
Bulb Type	LED amber
Rated Current	13 A at 250 V AC 50 Hz

Complementary

Load Type	Resistive
Number Of Cables	3 cable(s) 2.5 mm ² 1 cable(s) 2.5 mm ² 2 cable(s) 2.5 mm ² 1 cable(s) 4 mm ² 2 cable(s) 4 mm ²
Opening Distance	> 3 mm
Fixing Mode	By screws
Wiring Device Mounting	Surface Flush
Distance Between Centers	60.3 mm
Width	87 mm
Height	87 mm
Depth	31.8 mm

Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	<= 2000 m
Standards	BS 1363-2:1995 IEE 16th edition

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.5 cm
Package 1 Width	12.2 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	12.2 cm
Package 1 Weight	121.95 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	30
Package 2 Height	18 cm
Package 2 Width	31.2 cm
Package 2 Length	56.3 cm
Package 2 Weight	3658.5 g
Unit Type Of Package 3	PAL
Number Of Units In Package 3	600
Package 3 Height	100 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	73170 g

Contractual warranty

Warranty	18 months
----------	-----------