

Product data sheet

Specifications



APC Universal Transfer Switch 6-Circuit 120V

UTS6

⚠ Discontinued on: Oct 15, 2021

⚠ Discontinued

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	120 V
Main Output Voltage	120 V
Other Output Voltage	240 V
Input Connection Type	IEC 60320 C14 NEMA 5-15P NEMA L14-20P
Number Of Cables	1
Provided Equipment	Hardwire panel User manual Installation guide

Physical

Colour	Black
Height	49.8 cm
Width	39.4 cm
Depth	8.4 cm
Net Weight	9.77 kg
Mounting Location	Front Side Top
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Usb Compatible	No

Input

Network Frequency	47...63 Hz
Max Line Current	20 A

Conformance

Product Certifications	cTUVus
------------------------	--------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient Air Temperature For Operation	-25...40 °C
Relative Humidity	5...95 %
Operating Altitude	0...10000 ft
Ambient Air Temperature For Storage	-40...85 °C
Storage Altitude	0.00...3048.00 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	53.3 cm
Package 1 Width	44.5 cm
Package 1 Length	15.2 cm
Package 1 Weight	10.887 kg

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
