

# Product data sheet

Specifications



Switch disconnecter, TeSys Control, for ON/emergency stop, 12A(V02), 4 screws fixing, for mounting on door

VCF02

## Main

Range	TeSys
Product Name	TeSys VARIO
Device Short Name	VCF
Product Type	Emergency stop switch disconnecter

## Complementary

Device Composition	Switch Handle
Mounting Support	Handle: door Switch: door
Mounting Method	By 4 screws for handle
Performance Level	High performance
Number Of Poles	3P
Contact Type And Composition	3 NO
[Ue] Iec Rated Operational Voltage	690 V AC 50/60 Hz
Iec Rated Operational Power In W	3 kW at 400...415 V (AC-3) 4 kW at 500 V (AC-3) 1.5 kW at 230...240 V (AC-3) 5.5 kW at 500 V (AC-23A) 5.5 kW at 690 V (AC-3) 7.5 kW at 690 V (AC-23A) 3 kW at 230...240 V (AC-23A) 4 kW at 400...415 V (AC-23A)
[Ie] Rated Operational Current	8.1 A AC-23 Ue: 400 V
[Ith] Conventional Free Air Thermal Current	12 A
[Ithe] Conventional Enclosed Thermal Current	10 A
Making Capacity ( I Rms)	120 A at 400 V AC-21A 120 A at 400 V AC-22A 120 A at 400 V AC-23A
Breaking Capacity	120 A at 400 V (AC-21A) 120 A at 400 V (AC-22A) 120 A at 400 V (AC-23A)
Rated Conditional Short Circuit Current	10 kA at 400 V - associated fuse 12 A aM 10 kA at 400 V - associated fuse 12 A gG
[Icm] Rated Short Circuit Making Capacity	1 kA at 400 V at Ipeak
[Icw] Rated Short Time Withstand Current	300 A at 400 V duration: 1 s
[Uimp] Rated Impulse Withstand Voltage	8 kV

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Suitability For Isolation	Yes
Network Type	DC AC
Intermittent Duty Class	30
Control Type	Rotary handle
Rotary Handle Mounting Style	Direct
Handle Color	Red
Handle Front Plate Color	Yellow
Rotary Handle Padlocking	1 to 3 padlocks 4...8 mm
Marking	0 - 1
Mechanical Durability	100000 cycles
Electrical Durability	100000 cycles AC-21 30000 cycles DC-1 30000 cycles DC-2 30000 cycles DC-3 30000 cycles DC-4 30000 cycles DC-5
Iec Terminal Connection	Power circuit: screw clamp terminals10 mm² - solid Power circuit: screw clamp terminals6 mm² - flexible - with cable end
Tightening Torque	Power circuit: 2.1 N.m - on screw clamp terminals
Base Dimension	60 x 60 mm
Height	74 mm
Width	60 mm
Product Weight	0.25 kg

## Environment

Standards	IEC 60947-3
Product Certifications	UL CCC GL CSA UKCA
Degree Of Protection	IP20 conforming to IEC 60529 IP65
Protective Treatment	TC
Mechanical Robustness	Vibrations 10...150 Hz (1 gn) conforming to IEC 60068-2-6 Shocks 11 ms (30 Gn) conforming to IEC 60068-2-27
Ambient Air Temperature For Operation	-20...50 °C
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	Main switch disconnecter

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	9.000 cm
Package 1 Length	12.500 cm

Package 1 Weight	219.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	24
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.732 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	192
Package 3 Height	75.000 cm
Package 3 Width	60.000 cm
Package 3 Length	80.000 cm
Package 3 Weight	55.100 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

✓ Pvc Free

✓ Halogen Free Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Antimony oxide & Antimony trioxide, which is known to the State of California to cause cancer. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>