


# Product data sheet

Specifications

## Actassi 19-C Fixed Shelf 19" 1U 250mm Deep maximum 15kg



VDIG188011

### Main

Range	Actassi
Product	19" shelf
Provided Equipment	2 quick fix 19" mountings
Rack Unit	1U

### Complementary

Maximum Load	15 kg
Material	1.2 mm DC01
Colour	Dark grey
Width	490 mm
Height	45 mm
Depth	250 mm

### Environment

Standards	NF C 20-150 IEC 60297
Temperature Range	-10...55 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.400 cm
Package 1 Width	34.800 cm
Package 1 Length	54.400 cm
Package 1 Weight	1.471 kg
Unit Type Of Package 2	S04
Number Of Units In Package 2	5
Package 2 Height	30.000 cm
Package 2 Width	40.000 cm
Package 2 Length	60.000 cm
Package 2 Weight	8.172 kg
Unit Type Of Package 3	P12

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 3	20
Package 3 Height	45.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	42.864 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

 Reach Free Of Svhc

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Not applicable, out of EU RoHS legal scope

Environmental Disclosure

[Product Environmental Profile](#)

Circularity Profile

No need of specific recycling operations