


Product data sheet

Specifications



Actassi - traditional link with metallic splitter - LC/SC-OS2 - 2mm- Euroclass C

VDILL061K3K2

 **Discontinued on:** Feb 10, 2021

 **Discontinued**

Main

Range	Actassi
Product Or Component Type	Traditional link
Colour	LC connector: blue Sheath: yellow SC connector: blue
Type Of Packing	50...320 m cable drum

Complementary

Product Destination	empty fibre optic patch panel
Optic Fibre Type	Loose tube
Maximum Insertion Loss	0.3 dB 1310 nm 0.3 dB 1550 nm
Minimum Return Loss	45 dB 1310 nm 45 dB 1550 nm
Fibre Performance	OS2
Optic Fiber Diameter	2 mm
Sheath Type	Metallic cylinder
Condition Of Use	Indoor
Cable Outer Diameter	3.8 mm
Material	Plastic: LC connector Plastic: SC connector
Cable Length	1...500 m
Targeted Region	Europe

Environment

Ambient Air Temperature For Operation	-10...60 °C
Ambient Air Temperature For Storage	-25...70 °C
Euroclass Level	C

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards

Cable specification: IEC 60794-2
Cable test procedure: IEC 60794-1-2
Flame retardance: IEC 60332-1
IEC 60754-1
Acidity of combustion gases: IEC 60754-2
Smoke generation: IEC 61034
LC connector: IEC 61754-20
Performance: ISO/IEC 11801:2011 Ed.2.2
Cabling: ISO/IEC 24764
Fibre cabling test: ISO/IEC 14763-3
TIA/EIA-568-C.3
ANSI/TIA-942
10Gbase-SR: IEEE 802.3ae
SC connector: IEC 61754-4
SC connector: IEC 60874-19
Fibre performance: IEC 60793-2-10 Type B1.3
Fibre performance: IEC 60793-2-10 Type B6.A
Fibre performance: ITU G.652.D