

# Product data sheet

Specifications



## Actassi CL-MNC6 Patchcord U/UTP 4P Cat6 300MHz LSZH 0.5m Grey

VDIP181646005

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

### Main

Range	Actassi
Product	Patch cord
Colour	Patchcord: grey
Quantity Per Set	1
Cable Shielding Type	U/UTP
Provided Component	Grey coloured clips Green coloured clips Red coloured clips

### Complementary

Product Compatibility	Coloured clips red Coloured clips green Coloured clips yellow Coloured clips blue
Length (Customizable Value In Configurator)	0...0.5 m
Communication Network Type	10GBASE-T
Connector Type	RJ45
Communication Network Category	6
Transmission Frequency	300 MHz
Awg Gauge	AWG 24
Input Impedance	100 Ohm
Material	Solid bare copper: conductor PE (polyethylene): wire insulation
Targeted Region	Europe

### Environment

Ambient Air Temperature For Installation	0...50 °C
Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Temperature Resistance	60 °C
Flame Retardance	LSZH
Product Certifications	Delta

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	ISO/IEC 11801:2011 Ed.2.2
	IEC 61935-2
	EIA/TIA-568-C.2
	EN 50173 Ed.3

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	20 cm
Package 1 Width	19 cm
Package 1 Length	2.2 cm
Package 1 Weight	31 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations