


Product data sheet

Specifications



Renova - dimmer - 230 V - 630 W - white

WDE006913

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

Main

Range	Renova
Product Or Component Type	Dimmer
Device Application	Control
Device Presentation	Complete product
Dimmer Type	Transistor
Load Type	Incandescent lamp: 60...630 W 230 V AC halogen lamp: 60...600 W Low voltage halogen lamp with electronic transformer: 60...630 W
Quantity Per Set	Set of 1

Complementary

[Ue] Rated Operational Voltage	230 V AC 50 Hz
Rated Current	10 A
Power Range	20...630 VA
Switch Function	1-pole 2-way
Dimmer Control	Rotary push type
Protection Type	Short-circuit and overload protection with automatic reset
Connections - Terminals	Screw terminals
Number Of Loop Terminals	1
Shape Of Screw Head	Pozidriv No 1 and combi
Clamping Connection Capacity	1 x 1.5...2 x 2.5 mm ² for solid cable(s) 1 x 1.5...2 x 2.5 mm ² for solid stranded cable(s)
Material	PC/ABS
Surface Finish	Matt
Device Mounting	Flush
Fixing Mode	By screws
Diameter	83 mm
Depth	51 mm
Embedding Depth	29 mm
Projecting Depth	22 mm

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20 also with visual parts removed
Standards	EN 60669-2-1 EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.3 cm
Package 1 Width	8.3 cm
Package 1 Length	2.4 cm
Package 1 Weight	1 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations