

Product data sheet

Specifications



Safety limit switch, Telemecanique
Safety switches XCS, XCSM, metal,
roller plunger, 2 NC + 1 NO, cable 2
m

XCSM3702L2

Main

Range Of Product	Telemecanique Safety switches XCS
Product Or Component Type	Safety limit switch
Component Name	XCSM
Design	Miniature
Material	Metal
Head Type	Plunger head
Protection Technology	Plastic protective cover, secured by 5-lobe socket head safety screw
Type Of Approach	Lateral approach
Type Of Operator	Roller plunger
Contacts Type And Composition	1 NC + 1 NC + 1 NO
Contact Operation	Slow-break, break before make

Complementary

Electrical Connection	Pre-cabled
Cable Length	2 m
Cable Composition	7 x 0.5 mm ²
Switch Actuation	By 30° cam
Fixing Mode	By the body
Number Of Poles	3
Positive Opening	With NC contact
Mechanical Durability	10000000 cycles
Minimum Force For Tripping	7 N
Positive Opening Minimum Force	35 N
Minimum Actuation Speed	6 m/min
Maximum Actuation Speed	0.5 m/s
Contact Code Designation	B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN 60947-5-1 B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN/IEC 60947-5-1 appendix A R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN 60947-5-1 R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 appendix A
[Ui] Rated Insulation Voltage	300 V conforming to UL 508 400 V (pollution degree 3) conforming to IEC 60947-5-1 300 V conforming to CSA C22.2 No 14
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60664 4 kV conforming to IEC 60947-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Maximum Resistance Across Terminals	25 MOhm conforming to IEC 60255-7 category 3
Short-Circuit Protection	6 A cartridge fuse type gG (gl)
Repeat Accuracy	0.05 mm on the tripping points
Body Material	Zamak
Head Material	Zamak
Depth	16 mm
Height	70 mm
Width	30 mm
Net Weight	0.17 kg

Environment

Standards	EN/IEC 60947-5-1 UL 508 CSA C22.2 No 14 EN 1088 EN/IEC 60204-1
Product Certifications	UL CSA
Safety Level	Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1 Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508
Safety Reliability Data	B10d = 50000000 value given for a life time of 20 years limited by mechanical or contact wear
Protective Treatment	TC
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...70 °C
Vibration Resistance	25 gn (f= 10...500 Hz) conforming to IEC 60068-2-6
Shock Resistance	25 gn for 18 ms conforming to IEC 60068-2-27
Electrical Shock Protection Class	Class I conforming to NF C 20-030 Class I conforming to EN/IEC 61140
Ip Degree Of Protection	IP66 conforming to IEC 60529 IP67 conforming to IEC 60529 IP68 conforming to IEC 60529
Ik Degree Of Protection	IK06 conforming to EN 50102

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2 cm
Package 1 Width	19 cm
Package 1 Length	19 cm
Package 1 Weight	287 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	35
Package 2 Height	30 cm

Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	10.795 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	280
Package 3 Height	105 cm
Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	105.36 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

California Proposition 65
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov