

# Product data sheet

Specifications



## safety switch XCSTL - elbowed flush lever - centred - 3NC -Pg11

XCSTL881

⚠ Discontinued on: Jun 30, 2020

⚠ Discontinued

### Main

|                                |   |
|--------------------------------|---|
| Range Of Product               | Telemecanique Safety switches XCS                             |
| Product Or Component Type      | Guard switch  |
| Component Name                 | XCSTL   |
| Material                       | Plastic   |
| Head Type                      | Turret head rotary lever                                      |
| Insulation                     | Double insulated  |
| Type Of Operator               | Elbowed flush lever   |
| Operator Direction Information | Centred   |
| Electrical Connection          | Terminal  |
| Contacts Type And Composition  | 1 NC + 1 NC + 1 NC  |
| Contact Operation              | Slow-break  |
| Clamping Connection Capacity   | 1 x 0.34...2 x 0.75 mm <sup>2</sup> with or without cable end |
| Cable Entry                    | 2 entries tapped for Pg 11                                    |
| Number Of Poles                | 3   |

### Complementary

|  |  |
|--|--|
| Cable Outer Diameter                         | 7...10 mm  |
| Positive Opening                             | With NC contact  |
| Tripping Angle                               | 5 °  |
| Mechanical Durability                        | 1000000 cycles   |
| Minimum Torque For Tripping                  | 0.1 N.m  |
| Positive Opening Minimum Torque              | 0.45 N.m   |
| Minimum Actuation Speed                      | 0.1 m/s  |
| Contact Code Designation                     | B300, AC-15 (Ue = 120 V, Ie = 6 A) conforming to EN/IEC 60947-5-1<br>B300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1<br>Q300, DC-13 (Ue = 125 V, Ie = 0.2 A) conforming to EN/IEC 60947-5-1<br>R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 |
| [Ithe] Conventional Enclosed Thermal Current | 6 A  |
| [UI] Rated Insulation Voltage                | 300 V conforming to UL 508<br>300 V conforming to CSA C22.2 No 14<br>400 V (pollution degree 3) conforming to EN/IEC 60947-1   |
| [Uimp] Rated Impulse Withstand Voltage       | 4 kV conforming to EN/IEC 60947-5-1  |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |  |
|-------------------------------------|--|
| Maximum Resistance Across Terminals | 30 mOhm conforming to EN/IEC 60947-5-4   |
| Short-Circuit Protection            | 6 A cartridge fuse type gG (gl)  |
| Safety Level                        | Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1<br>Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1<br>Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508 |
| Safety Reliability Data             | B10d = 5000000 value given for a life time of 20 years limited by mechanical or contact wear   |
| Enclosure Material                  | Polyamide PA66 fibre glass impregnated   |
| Lever Material                      | Stainless steel  |
| Width                               | 52 mm  |
| Height                              | 181 mm   |
| Depth                               | 30 mm  |
| Net Weight                          | 0.145 kg   |

## Environment

|                                       |  |
|---------------------------------------|--|
| Standards                             | EN/IEC 60947-5-1<br>CSA C22.2 No 14<br>EN 1088/ISO 14119<br>UL 508<br>EN/IEC 60947-5-4<br>EN/IEC 60204-1<br>EN/ISO 12100 |
| Product Certifications                | BG<br>UL<br>CSA  |
| Protective Treatment                  | TC<br>TH   |
| Ambient Air Temperature For Operation | -25...70 °C  |
| Ambient Air Temperature For Storage   | -40...70 °C  |
| Vibration Resistance                  | 50 gn (f= 10...500 Hz) conforming to IEC 60068-2-6   |
| Shock Resistance                      | 50 gn for 11 ms conforming to IEC 60068-2-27   |
| Electrical Shock Protection Class     | Class II conforming to EN/IEC 61140  |
| Ip Degree Of Protection               | IP67 conforming to IEC 60529   |

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type Of Package 1       | PCE    |
| Number Of Units In Package 1 | 1      |
| Package 1 Height             | 3.2 cm |
| Package 1 Width              | 20 cm  |
| Package 1 Length             | 6.3 cm |
| Package 1 Weight             | 225 g  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

## Certifications & Standards

|                   |   |
|-------------------|---|
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a> |
|-------------------|---|

|                           |  |
|---------------------------|--|
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |
|---------------------------|--|