

# Product data sheet

Specifications



Head for double headed push button, Harmony XB5, 1 green flush, 1 red projecting, 22mm, spring return, unmarked

ZB5AL7340

## Main

|                               |                                     |
|-------------------------------|-------------------------------------|
| Range Of Product              | Harmony XB5                         |
| Product Or Component Type     | Head for double-headed push-button  |
| Device Short Name             | ZB5                                 |
| Bezel Material                | Dark grey plastic                   |
| Mounting Diameter             | 22 mm                               |
| Head Type                     | Standard                            |
| Sale Per Indivisible Quantity | 1                                   |
| Shape Of Signaling Unit Head  | Rectangular                         |
| Type Of Operator              | spring return                       |
| Operator Profile              | 1 flush - 1 projecting push-buttons |
| Operators Description         | Green unmarked - red unmarked       |

## Complementary

|                             |   |
|-----------------------------|---|
| Cad Overall Width           | 30 mm   |
| Cad Overall Height          | 50 mm   |
| Cad Overall Depth           | 35 mm   |
| Net Weight                  | 0.023 kg  |
| Colour Of Marking           | White marking when green, red or black caps<br>Black marking when white caps  |
| Operator Profile            | Green flush, unmarked<br>Red projecting, unmarked   |
| Mechanical Durability       | 1000000 cycles  |
| Station Name                | XALD 1 cut-out  |
| Electrical Composition Code | C3 for <6 contacts using single blocks in front mounting<br>C4 for <6 contacts using single and double blocks in front mounting<br>C14 for <2 contacts using single blocks in front mounting<br>SF2 for <2 contacts using single blocks in front mounting<br>SR2 for <2 contacts using single blocks in rear mounting |
| Device Presentation         | Basic element   |

## Environment

|                                       |             |
|---------------------------------------|-------------|
| Protective Treatment                  | TH          |
| Ambient Air Temperature For Storage   | -40...70 °C |
| Ambient Air Temperature For Operation | -25...70 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                    |  |
|------------------------------------|--|
| Electrical Shock Protection Class  | Class II conforming to IEC 60536   |
| Ip Degree Of Protection            | IP66 conforming to IEC 60529<br>IP69K conforming to IEC 60529  |
| Nema Degree Of Protection          | NEMA 13<br>NEMA 4X   |
| Resistance To High Pressure Washer | 7000000 Pa at 55 °C, distance : 0.1 m  |
| Ik Degree Of Protection            | IK03 conforming to IEC 50102   |
| Standards                          | EN/IEC 60947-5-4<br>EN/IEC 60947-5-1<br>JIS C8201-5-1<br>EN/IEC 60947-1<br>UL 508<br>CSA C22.2 No 14<br>JIS C8201-1  |
| Product Certifications             | BV<br>DNV<br>CSA<br>GL<br>LROS (Lloyds register of shipping)<br>UL listed  |
| Vibration Resistance               | 5 gn (f= 2...500 Hz) conforming to IEC 60068-2-6   |
| Shock Resistance                   | 30 gn (duration = 18 ms) for half sine wave acceleration conforming to IEC 60068-2-27<br>50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 4.5 cm  |
| Package 1 Width              | 3.3 cm  |
| Package 1 Length             | 5.3 cm  |
| Package 1 Weight             | 25.0 g  |
| Unit Type Of Package 2       | S01     |
| Number Of Units In Package 2 | 75      |
| Package 2 Height             | 15.0 cm |
| Package 2 Width              | 15.0 cm |
| Package 2 Length             | 40.0 cm |
| Package 2 Weight             | 2.1 kg  |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)


## Certifications & Standards

|                           |   |
|---------------------------|---|
| Reach Regulation          | <a href="#">REACH Declaration</a>   |
| Eu Rohs Directive         | Pro-active compliance (Product out of EU RoHS legal scope)  |
| China Rohs Regulation     | <a href="#">China RoHS declaration</a>  |
| Environmental Disclosure  | <a href="#">Product Environmental Profile</a>   |
| Circularity Profile       | <a href="#">End of Life Information</a>   |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a> |


Dimensions Drawings

Dimensions

Without Boot



With Boot ZBA710



Mounting and Clearance

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)


Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board



- (1) Diameter on finished panel or support  
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  
(3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

| Connections                                   | a in mm | a in in. | b in mm | b in in. |
|---|---------|----------|---------|----------|
| By screw clamp terminals or plug-in connector | 40      | 1.57     | 30      | 1.18     |
| By Faston connectors                          | 45      | 1.77     | 32      | 1.26     |
| On printed circuit board                      | 30      | 1.18     | 30      | 1.18     |


Detail of Lug Recess



- (1) Diameter on finished panel or support  
(2) For selector switches and Emergency stop buttons, use of an anti-rotation plate type ZB5AZ902 is recommended.  
(3) Ø22.5 mm recommended ( $\text{Ø}22.3 \begin{smallmatrix} +0.4 \\ 0 \end{smallmatrix}$ ) / Ø0.89 in. recommended ( $\text{Ø}0.88 \text{ in. } \begin{smallmatrix} +0.016 \\ 0 \end{smallmatrix}$ )

Pushbuttons, Switches and Pilot Lights for Printed Circuit Board Connection

Panel Cut-outs (Viewed from Installer’s Side)



A: 30 mm min. / 1.18 in. min.  
B: 40 mm min. / 1.57 in. min.

Printed Circuit Board Cut-outs (Viewed from Electrical Block Side)

Dimensions in mm



A: 30 mm min.  
B: 40 mm min.  
Dimensions in in.



A: 1.18 in. min.  
B: 1.57 in. min.


General Tolerances of the Panel and Printed Circuit Board

The cumulative tolerance must not exceed 0.3 mm / 0.012 in.: T1 + T2 = 0.3 mm max.

Installation Precautions

- Minimum thickness of circuit board: 1.6 mm / 0.06 in.
- Cut-out diameter: 22.4 mm ± 0.1 / 0.88 in. ± 0.004
- Orientation of body/fixing collar ZB5AZ009: ± 2° 30' (excluding cut-outs marked a and b).
- Tightening torque of screws ZBZ006: 0.6 N.m (5.3 lbf.in) max.
- Allow for one ZB5AZ079 fixing collar/pillar and its fixing screws:
  - every 90 mm / 3.54 in. horizontally (X), and 120 mm / 4.72 in. vertically (Y).
  - with each selector switch head (ZB5AD•, ZB5AJ•, ZB5AG•).

The fixing centers marked a and b are diagonally opposed and must align with those marked 4 and 5.



- (1) Head ZB5AD•
- (2) Panel
- (2) Nut
- (4) Printed circuit board

Mounting of Adapter (Socket) ZBZ01•

- 1 2 elongated holes for ZBZ006 screw access
- 2 1 hole Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 for centring adapter ZBZ01•
- 3 8 × Ø 1.2 mm / 0.05 in. holes
- 4 1 hole Ø 2.9 mm ± 0.05 / 0.11 in. ± 0.002, for aligning the printed circuit board (with cut-out marked a)
- 5 1 elongated hole for aligning the printed circuit board (with cut-out marked b)
- 6 4 holes Ø 2.4 mm / 0.09 in. for clipping in adapter ZBZ01•

Dimensions An + 18.1 relate to the Ø 2.4 mm ± 0.05 / 0.09 in. ± 0.002 holes for centring adapter ZBZ01•.

Technical Description

Electrical Composition Corresponding to Code C3

---



Electrical Composition Corresponding to Code C4

---



Electrical Composition Corresponding to Codes C14, SF2 and SR2

---



Legend

---

Single contact



Double contact



Light block



Possible location

