

Product data sheet

Specifications



Inductive proximity sensors XS,
inductive sensor XS5 M8, L51mm,
stainless, Sn1.5 mm, 12...48 VDC,
cable 2 m

XS508B1DAL2

Main

Range Of Product	Telemecanique Inductive proximity sensors XS
Series Name	General purpose
Sensor Type	Inductive proximity sensor
Device Application	-
Sensor Name	XS5
Sensor Design	Cylindrical M8
Size	51 mm
Body Type	Fixed
Detector Flush Mounting Acceptance	Flush mountable
Material	Stainless steel
Type Of Output Signal	Discrete
Wiring Technique	2-wire
[Sn] Nominal Sensing Distance	1.5 mm
Discrete Output Function	1 NO
Output Circuit Type	DC
Electrical Connection	Cable
Cable Length	2 m
[Us] Rated Supply Voltage	12...48 V DC
Switching Capacity In Ma	1.5...100 mA DC with overload and short-circuit protection
Ip Degree Of Protection	IP67 conforming to IEC 60529

Complementary

Thread Type	M8 x 1
Detection Face	Frontal
Front Material	PPS
Enclosure Material	Stainless steel 303
Operating Zone	0...1.2 mm
Differential Travel	1...15% of Sr
Cable Composition	2 x 0.11 mm²
Wire Insulation Material	PVC
Status Led	Output state: 1 LED (yellow)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Supply Voltage Limits	10...58 V DC
Maximum Residual Current	0.5 mA open state
Switching Frequency	<= 4000 Hz
Maximum Voltage Drop	<4 V (closed)
Maximum Delay First Up	10 ms
Maximum Delay Response	0.2 ms
Maximum Delay Recovery	0.2 ms
Marking	CE
Threaded Length	42 mm
Length	51 mm
Net Weight	0.035 kg

Environment

Product Certifications	UL CCC CSA
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Vibration Resistance	25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.200 cm
Package 1 Width	9.700 cm
Package 1 Length	13.200 cm
Package 1 Weight	39.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	44
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	2.275 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)


Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

Circularity Profile [End of Life Information](#)

California Proposition 65
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings

Dimensions




(1) LED

Mounting and Clearance


Minimum Mounting Distances

Side by side




$e (1) \geq 3 \text{ mm}/0.12 \text{ in.}$

Face to face




$e (2) \geq 18 \text{ mm}/0.71 \text{ in.}$

Facing a metal object



$e (3) \geq 4.5 \text{ mm}/0.18 \text{ in.}$

Mounting




(1) Bending cable: 4 x external cable diameter

Connections and Schema

Wiring Schemes

2-Wire Non-polarised

NO output




BU : Blue
BN : Brown

Performance Curves

Performance Curves

Standard Steel Target : 8x8x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm