

Product data sheet

Specifications



Inductive proximity sensors XS,
inductive sensor XS5 M30, L43mm,
brass, Sn10mm, 12...24 VDC, cable
2 m

XS530B1NAL2

Main

Range Of Product	Telemecanique Inductive proximity sensors XS
Series Name	General purpose
Sensor Type	Inductive proximity sensor
Device Application	-
Sensor Name	XS5
Sensor Design	Cylindrical M30
Size	43 mm
Body Type	Fixed
Detector Flush Mounting Acceptance	Flush mountable
Material	Metal
Type Of Output Signal	Discrete
Wiring Technique	3-wire
[Sn] Nominal Sensing Distance	10 mm
Discrete Output Function	1 NO
Output Circuit Type	DC
Discrete Output Type	NPN
Electrical Connection	Cable
Cable Length	2 m
[Us] Rated Supply Voltage	12...24 V DC with reverse polarity protection
Switching Capacity In Ma	<= 200 mA DC with overload and short-circuit protection
Ip Degree Of Protection	IP68 double insulation conforming to IEC 60529 IP69K conforming to DIN 40050

Complementary

Thread Type	M30 x 1.5
Detection Face	Frontal
Front Material	PPS
Enclosure Material	Nickel plated brass
Operating Zone	0...8 mm
Differential Travel	1...15% of Sr
Cable Composition	3 x 0.34 mm²

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Wire Insulation Material	PVC
Status Led	Output state: 1 LED (yellow)
Supply Voltage Limits	10...36 V DC
Switching Frequency	<= 1000 Hz
Maximum Voltage Drop	<2 V (closed)
Current Consumption	<= 10 mA no-load
Maximum Delay First Up	10 ms
Maximum Delay Response	0.3 ms
Maximum Delay Recovery	0.7 ms
Marking	CE
Threaded Length	32 mm
Length	43 mm
Net Weight	0.205 kg

Environment

Product Certifications	CSA UL
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Vibration Resistance	25 gn amplitude = +/- 2 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Shock Resistance	50 gn for 11 ms conforming to IEC 60068-2-27

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.2 cm
Package 1 Width	9.6 cm
Package 1 Length	13.2 cm
Package 1 Weight	179 g

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)


Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

Circularity Profile [End of Life Information](#)

California Proposition 65
WARNING: This product can expose you to chemicals including: Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Dimensions Drawings


Dimensions




Mounting and Clearance

Minimum Mounting Distances


Side by side



$e (1) \geq 20 \text{ mm}/0.79 \text{ in}$
Face to face



$e (2) \geq 120 \text{ mm}/4.72 \text{ in}$
Facing a metal object




$e (3) \geq 30 \text{ mm}/1.18 \text{ in.}$

Connections and Schema

Wiring Schemes

NPN




BU : Blue
BN : Brown
BK : Black

Performance Curves

Performance Curves

Standard Steel Target : 30x30x1 mm



- (1) Pick-up points
- (2) Drop-out points (object approaching from the side)
- (y) Sensing distance in mm