

Product data sheet

Specifications



Ø 45 mm tower light - steady - yellow - IP40

XVDLS38

⚠ Discontinued on: Apr 17, 2020

⚠ Discontinued

Main

| | |
|------------------------------------|--|
| Range Of Product | Harmony XVD Optimum |
| Product Or Component Type | Complete miniature beacon |
| Beacon Or Indicator Bank Unit Type | Base unit direct fixing Illuminated unit |
| Signalling Type | Steady |
| Mounting Diameter | 45 mm |
| Component Name | XVDLS |
| Material | Glass reinforced polyamide: base unit Polycarbonate: illuminated unit |
| Light Source | Bulb not included, yellow |
| Bulb Type | Incandescent with BA 15d base |
| [Us] Rated Supply Voltage | <= 230 V |
| Maximum Power Dissipation In W | 5 W |

Complementary

| | |
|--|--|
| Connections - Terminals | Screw clamp terminals, <= 1 x 1.5 mm² with cable end |
| Cable Entry | 1 entry tapped for Pg 7 |
| [Ui] Rated Insulation Voltage | 250 V conforming to IEC 60947-1 |
| [Uimp] Rated Impulse Withstand Voltage | 4 kV conforming to IEC 60947-1 |
| Cad Overall Width | 45 mm |
| Cad Overall Height | 104 mm |
| Cad Overall Depth | 45 mm |
| Terminals Description Iso N°1 | (COM-1)PW (GND)GROUND |
| Net Weight | 0.08 kg |

Environment

| | |
|---------------------------------------|------------------|
| Product Certifications | CSA UL |
| Standards | EN/IEC 60947-5-1 |
| Protective Treatment | TC |
| Ambient Air Temperature For Operation | -25...70 °C |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------------------------|----------------------------------|
| Ambient Air Temperature For Storage | -40...70 °C |
| Electrical Shock Protection Class | Class II conforming to IEC 60536 |
| Ip Degree Of Protection | IP40 conforming to IEC 60529 |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)


Certifications & Standards

| | |
|---------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration |
| Environmental Disclosure | Product Environmental Profile |
| Weee | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |
| Circularity Profile | No need of specific recycling operations |
| California Proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |

Dimensions Drawings

Illuminated Beacon

Dimensions



Mounting and Clearance

Illuminated Beacon

Panel Cut-out for Direct Fixing

