


Product datasheet

Specifications



MODULAR FRONT PLATE WIDTH 600/650 3M

03203

! Discontinued on: 15 Jun 2023

! Discontinued

Price: 453.53 ZAR

Main

Range	Prisma
Range Of Product	Prisma G Prisma P
Product Or Component Type	Front plate
Accessory / Separate Part Category	Installation accessory
Range Compatibility	Prisma Prisma G enclosure Prisma Prisma P cubicle Prisma Prisma Pack 250 enclosure
Type Of Front Plate	Cut-out Modular
Installed Device	TeSys: fixed GV2L TeSys: fixed GV2LE TeSys: fixed GV2ME TeSys: fixed GV2P TeSys: fixed GV2RTn Vigilohm: IM20 Vigilohm: IM20H Vigilohm: fixed IM9 Vigilohm: IM9 Vigilohm: fixed IM9-OL Vigilohm: IM9-OL Acti 9: measurement device Multi9: measurement device Acti 9: fixed modular device <= 40 A Multi9: fixed modular device <= 40 A Vigirex: RH10 Vigirex: RH197M Vigirex: RH21 Vigirex: RH99

Poles Description	9 x 3P: modular rail support: GV2L 9 x 3P: modular rail support: GV2LE 9 x 3P: modular rail support: GV2ME 9 x 3P: modular rail support: GV2P 9 x 3P: modular rail support: GV2RTn
-------------------	--

Complementary

Enclosure/Cubicle Description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm Cubicle - width 650 mm depth 400 mm Pack enclosure - width 555 mm Pack enclosure - width 600 mm
9 Mm Pitches	48
Number Of 18 Mm Modules Per Row	24
Number Of Vertical Modules [50 Mm]	3

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61439-1 IEC 61439-2
Product Certifications	ASEFA
Material	Steel
Surface Finish	Matt Smooth
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9001)
Height	150 mm
Width	500 mm
Net Weight	0.54 kg
Quantity Per Set	Set of 1
Functional Unit	600 mm Prisma G floor-standing enclosure TeSys GV2L fixed 3P 9 direct 3 600 mm Prisma G wall-mounted enclosure TeSys GV2L fixed 3P 9 direct 3 650 mm 400 mm Prisma P cubicle TeSys GV2L fixed 3P 9 direct 3 600 mm Prisma G floor-standing enclosure TeSys GV2LE fixed 3P 9 direct 3 600 mm Prisma G wall-mounted enclosure TeSys GV2LE fixed 3P 9 direct 3 650 mm 400 mm Prisma P cubicle TeSys GV2LE fixed 3P 9 direct 3 600 mm Prisma G floor-standing enclosure TeSys GV2ME fixed 3P 9 direct 3 600 mm Prisma G wall-mounted enclosure TeSys GV2ME fixed 3P 9 direct 3 650 mm 400 mm Prisma P cubicle TeSys GV2ME fixed 3P 9 direct 3 600 mm Prisma G floor-standing enclosure TeSys GV2P fixed 3P 9 direct 3 600 mm Prisma G wall-mounted enclosure TeSys GV2P fixed 3P 9 direct 3 650 mm 400 mm Prisma P cubicle TeSys GV2P fixed 3P 9 direct 3 600 mm Prisma G floor-standing enclosure TeSys GV2RTn fixed 3P 9 direct 3 600 mm Prisma G wall-mounted enclosure TeSys GV2RTn fixed 3P 9 direct 3 650 mm 400 mm Prisma P cubicle TeSys GV2RTn fixed 3P 9 direct 3 600 mm Prisma G floor-standing enclosure Vigilohm 4 3 600 mm Prisma G wall-mounted enclosure Vigilohm 4 3 600 mm Prisma G floor-standing enclosure Vigilohm fixed 6 3 600 mm Prisma G wall-mounted enclosure Vigilohm fixed 6 3 650 mm 400 mm Prisma P cubicle Vigilohm 6 3 650 mm 400 mm Prisma P cubicle Acti 9 measurement device 3 650 mm 400 mm Prisma P cubicle Multi9 measurement device 3 600 mm Prisma G floor-standing enclosure Acti 9 modular device <= 40 A fixed 48 direct 3 600 mm Prisma G wall-mounted enclosure Acti 9 modular device <= 40 A fixed 48 direct 3 650 mm 400 mm Prisma P cubicle Acti 9 modular device <= 40 A fixed 48 direct 3 600 mm Prisma G floor-standing enclosure Multi9 modular device <= 40 A fixed 48 direct 3 600 mm Prisma G wall-mounted enclosure Multi9 modular device <= 40 A fixed 48 direct 3 650 mm 400 mm Prisma P cubicle Multi9 modular device <= 40 A fixed 48 direct 3 600 mm Prisma G floor-standing enclosure Vigirex 8 direct 3 600 mm Prisma G wall-mounted enclosure Vigirex 8 direct 3 650 mm 400 mm Prisma P cubicle Vigirex 8 3 650 mm 400 mm Prisma P cubicle Vigirex 6 3 600 mm Prisma Pack 250 Pack enclosure Acti 9 modular device <= 40 A fixed 48 direct 6 600 mm Prisma Pack 250 Pack enclosure Multi9 modular device <= 40 A fixed 48 direct 6

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3.0 cm
Package 1 Width	16.0 cm
Package 1 Length	52.0 cm
Package 1 Weight	540.0 g
Unit Type Of Package 2	BB1

Number Of Units In Package 2	10
Package 2 Height	17.5 cm
Package 2 Width	17.0 cm
Package 2 Length	53.0 cm
Package 2 Weight	5.56 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	450
Package 3 Height	102.0 cm
Package 3 Width	80.0 cm
Package 3 Length	120.0 cm
Package 3 Weight	285.4 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓	Reach Free Of Svhc	
✓	Toxic Heavy Metal Free	
✓	Mercury Free	
✓	Rohs Exemption Information	Yes
✓	Halogen Free Plastic Parts Product	

Certifications & Standards

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile