# **Product datasheet**

Specifications



# DUCT (REAR ENCLOSURE+PLAIN DOOR) W300 15M PRISMA G IP55

08344

() Discontinued on: 15 Jun 2023

#### Main

Range	Prisma
Range Of Product	Prisma G
Product Or Component Type	Rear panel Door
Device Application	Low voltage electrical distribution
Enclosure Type	Functional enclosure delivered in kit form
Enclosure Mounting	Surface
Provided Equipment	1 x door for enclosure
Additional Information	Can be combined side by side and one on top of another
Type Of Front Plate	Without
Number Of Vertical Modules [50 Mm]	15
Number Of 18 Mm Modules Per Row	10
Standards	IEC 62208 IEC 61439-2 IEC 61439-1

### Complementary

[Ui] Rated Insulation Voltage	1000 V
[In] Rated Current	630 A at 40 °C conforming to IEC 61439-2
Electrical Insulation Class	Class I
Protective Treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Surface Finish	Smooth Matt
Colour	White (RAL 9001)
Width	300 mm
Height	850 mm
Depth	260 mm
Net Weight	15.04 kg
Quantity Per Set	Set of 1

#### Environment

Ip Degree Of Protection

IP55 with door

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Ik Degree Of Protection	IK10 with door conforming to EN/IEC 62262
Mechanical Robustness	Seismic tests - 2.5G conforming to IEC 60068-2-57

# Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.000 cm
Package 1 Width	37.000 cm
Package 1 Length	84.000 cm
Package 1 Weight	14.571 kg
Unit Type Of Package 2	P12
Number Of Units In Package 2	4
Package 2 Height	37.000 cm
Package 2 Width	80.000 cm
Package 2 Length	120.000 cm
Package 2 Weight	60.160 kg

Life Is On Scheider

# Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile