Product datasheet

Specifications





residual current protection relay, VigiPacT RH10P, 500 mA, 12/24 VAC 50/60 Hz, 12/48 VDC, front panel mounting

56206

() Discontinued on: 07 Jan 2021

(!) End-of-service on: 28 Feb 2021

Main

mann	
Range	VigiPacT
Device Short Name	RH10P
Product Or Component Type	Residual current protection relay
Relay Application	Protection relay
Mounting Support	Front panel
Earth-Leakage Protection Class	Туре А
Type Of Setting	None
Residual Earth-Leakage Sensitity Adjustment Type	Fixed
Earth-Leakage Sensitivity	0.5 A
Earth-Leakage Time Delay	Instantaneous
Current Sensors Compatibility	VigiPacT TOA earth leakage current sensor VigiPacT A earth leakage current sensor VigiPacT L earth leakage current sensor
[Ithe] Conventional Enclosed Thermal Current	8 A
Minimum Load	10 mA at 12 V
[Us] Rated Supply Voltage	1224 V AC 50/60 Hz 55120 % 1248 V DC 55120 %
Power Consumption In Va	4 VA
Monitored Distribution System	1000 V - AC at 50/60 Hz (maximum) 1000 V - AC at 400 Hz (maximum)
Earthing System	TN-S TT IT
[Uimp] Rated Impulse Withstand Voltage	8 kV
Reset	Manual reset

Complementary

Test Function	Local Remote test
Monitoring	Electronics (continuous) Power supply (continuous) Relay/sensor link (continuous)
Type Of Measurement	Earth fault current internal measurement, range: 80100 %

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Tamperproof Of Settings	Protected by sealable cover
Connections - Terminals	Auxiliary power supply: terminal block cable(s) 0.22.5 mm ² flexible AWG 24AWG 12
	Auxiliary power supply: terminal block cable(s) 0.22.5 mm ² rigid AWG 24AWG 12
	Auxiliary power supply: terminal block cable(s) 0.252.5 mm ² flexible AWG
	24AWG 12
	Fault: terminal block cable(s) 0.22.5 mm ² flexible AWG 24AWG 12
	Fault: terminal block cable(s) 0.22.5 mm ² rigid AWG 24AWG 12
	Fault: terminal block cable(s) 0.252.5 mm ² flexible AWG 24AWG 12
	Relay test and fault reset: terminal block cable(s) 0.22.5 mm ² flexible AWG 24AWG 12
	Relay test and fault reset: terminal block cable(s) 0.22.5 mm ² rigid AWG 24AWG
	12
	Relay test and fault reset: terminal block cable(s) 0.252.5 mm² flexible AWG
	24AWG 12
	Sensor: terminal block cable(s) 0.22.5 mm ² flexible AWG 24AWG 12
	Sensor: terminal block cable(s) 0.22.5 mm ² rigid AWG 24AWG 12
	Sensor: terminal block cable(s) 0.252.5 mm ² flexible AWG 24AWG 12
	Voltage presence: terminal block cable(s) 0.22.5 mm ² flexible AWG 24AWG 12
	Voltage presence: terminal block cable(s) 0.22.5 mm ² rigid AWG 24AWG 12 Voltage presence: terminal block cable(s) 0.25 - 2.5 mm ² flexible AWG 24 - AWG 12
	Voltage presence: terminal block cable(s) 0.252.5 mm ² flexible AWG 24AWG 12
Wire Stripping Length	Auxiliary power supply: 7 mm
	Fault: 7 mm
	Relay test and fault reset: 7 mm
	Sensor: 7 mm
	Voltage presence: 7 mm
Fightening Torque	Auxiliary power supply: 0.6 N.m
	Fault: 0.6 N.m
	Relay test and fault reset: 0.6 N.m
	Sensor: 0.6 N.m
	Voltage presence: 0.6 N.m
Standards	EN/IEC 60947-2 Annex M
	EN/IEC 60755
	UL 1053
	CAN/CSA C22.2 No. 144
Width	72 mm
Height	72 mm
Depth	78 mm
Cut-Out Dimensions	68 x 68 mm
Net Weight	0.3 kg
p Degree Of Protection	IP40 on front face: conforming to EN/IEC 60529
	IP30 on side parts: conforming to EN/IEC 60529
	IP20 on connection terminals: conforming to EN/IEC 60529
k Degree Of Protection	IK07 conforming to EN 50102
Mechanical Robustness	Fire resistance conforming to IEC 60695-2-1
inconanioal hobustices	IK protection 2 joules: IK07 conforming to EN 50102
	Vibrations 13.2100 Hz: 0.7 g

Environment

Overvoltage Category	IV
Electrical Shock Protection Class	Class II
Electromagnetic Compatibility	Conducted and radiated emissions: , B, conforming to CISPR 11 Conducted radio-frequency immunity test: , 3, conforming to IEC 61000-4-6 Electrostatic discharge immunity test: , 4, conforming to IEC 61000-4-2 High-energy conducted susceptibility: , 4, conforming to IEC 61000-4-5 Low-energy conducted susceptibility: , 4, conforming to IEC 61000-4-4 Radiated susceptibility: , 3, conforming to IEC 61000-4-3
Relative Humidity	95 % at 55 °C
Pollution Degree	3 conforming to IEC 60664-1

Ambient Air Temperature For Operation	-3570 °C
Ambient Air Temperature For Storage	-5585 °C
Packing Units	

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Contractual warranty

Warranty

18 months

Sustainability Screen

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



RoHS/REACh

Well-being performance

Mercury Free

Rohs Exemption Information Yes

Certifications & Standards

Eu Rohs Directive	Compliant
	EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins