# **Product datasheet**

Specifications





I/O module MES120 - Sepam series 60, 80 - 14 inputs+ 6 outputs 24...250V DC

59715

Price: 15,492.25 ZAR

## Main

Module Type	Input/output module
Range Of Product	Sepam series 80 Sepam series 60
Device Short Name	MES120

## Complementary

Input/Output Type	14 inputs + 6 outputs 24250 V at DC
Logic Input Number	14 24250 V 19.2275 V DC 3 mA 14 V enhanced
Number Of Outputs	1 control relay 5 annunciation relay
Output Type	Annunciation relay: 100240 V AC 47.563 Hz continuous current: 2 A breaking

capacity:  $0.001 \text{ kA } \cos \varphi > 0.3$ 

Annunciation relay: 127 V DC continuous current: 2 A breaking capacity: 0.0005 kA L/R < 20 ms

Annunciation relay: 220 V DC continuous current: 2 A breaking capacity: 0.00015 kA L/R < 20 ms

Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 0.002 kA L/R

< 20 ms Annunciation relay: 250 V DC continuous current: 2 A breaking capacity: 0.0002 kA

L/R < 20 msAnnunciation relay: 48 V DC continuous current: 2 A breaking capacity: 0.001 kA L/R < 20 ms

Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.005 kA cos  $\phi$  > 0.3 making capacity: < 15 A for 200 ms

Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms

Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 40 ms making capacity: < 15 A for 200 ms

Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0005 kA L/R < 20 ms making capacity: < 15 A for 200 ms

Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0007 kA resistive making capacity: < 15 A for 200 ms

Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0001 kA L/R < 40 ms making capacity: < 15 A for 200 ms

Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 20 ms making capacity: < 15 A for 200 ms

Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0003 kA resistive making capacity: < 15 A for 200 ms

Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.004 kA L/R < 40 ms making capacity: < 15 A for 200 ms

Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.006 kA L/R < 20 ms making capacity: < 15 A for 200 ms

Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms

Control relay: 250 V DC continuous current: 8 A breaking capacity: 0.0002 kA resistive making capacity: < 15 A for 200 ms

Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.001 kA L/R < 40 ms making capacity: < 15 A for 200 ms

Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.002 kA L/R < 20 ms making capacity: < 15 A for 200 ms

Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.004 kA resistive making capacity: < 15 A for 200 ms

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy'

Height	170 mm
Width	40 mm
Depth	120 mm
Net Weight	0.38 kg
Mechanical Robustness	Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3
	Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3
	Jolts de-energized (level: 2): 20 Gn/16 ms conforming to IEC 60255-21-2
	Shocks de-energized (level: 2): 27 Gn/11 ms conforming to IEC 60255-21-2
	Shocks in operation (level: 2): 10 Gn/11 ms conforming to IEC 60255-21-2
	Vibrations de-energized (level: 2): 2 Gn, 10 Hz150 Hz conforming to IEC 60255-21-1
	Vibrations in operation (level: 2): 1 Gn, 10 Hz150 Hz conforming to IEC 60255-21-1
	Vibrations in operation (level: Fc) : 2 Hz13.2 Hz, a = $\pm$ 1 mm conforming to IEC 60068-2-6
Auxiliary Connection Terminal	Screw-type connectors1 cable(s) 0.22.5 mm²
	Screw-type connectors1 cable(s) 1.5 mm²
	Screw-type connectors1 cable(s) 2.5 mm <sup>2</sup>
	Screw-type connectors2 cable(s) 0.21 mm²
	Screw-type connectors2 cable(s) 1 mm²

### **Environment**

#### **Electromagnetic Compatibility**

1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV DM, conforming to IEC 60255-22-1

1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 2.5 kV DM, conforming to ANSI C37.90.1

100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV DM, conforming to IEC 61000-4-12

Conducted disturbance emission: (emission tests), conforming to IEC 60255-25 Conducted disturbance emission: (emission tests), A, conforming to EN 55022 Disturbing field emission: (emission tests), conforming to IEC 60255-25 Disturbing field emission: (emission tests), A, conforming to EN 55022

Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV contact, conforming to ANSI C37.90.3

Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2

Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1

Fast transient bursts: (immunity tests-conducted disturbances), A and B, 4kV, 2.5 kHz/2 kV, 5 kHz, conforming to IEC 60255-22-4

Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, conforming to IEC 61000-4-4

Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), III, 10 V, conforming to IEC 60255-22-6

Immunity to magnetic fields at network frequency: (immunity tests-radiated disturbances), IV, 30 A/m (continuous)-300 A/m (1-3 s), conforming to IEC 61000-4-8 Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz... 1 GHz, conforming to IEC 60255-22-3

Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz... 1 GHz, conforming to ANSI C37.90.2

Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 MHz...2 GHz, conforming to IEC 61000-4-3

Surges: (immunity tests-conducted disturbances), III, 2 kV CM, 1 kV DM, conforming to IEC 61000-4-5

Voltage interruptions: (immunity tests-conducted disturbances), 100 % during 100 ms, conforming to IEC 60255-11

Climatic Withstand

Influence of corrosion/gaz test 2 (in operation) : 21 days, 75 % RH, 25  $^{\circ}$ C, 0.5 ppm H2S, 1 ppm S02 conforming to IEC 60068-2-60

Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm H2S, 0.2 ppm S02, 0.2 ppm NO2, 0.01 ppm Cl2 conforming to IEC 60068-2-60 Continuous exposure to damp heat (in operation) : Cab: 10 days, 93 % RH, 40 °C

conforming to IEC 60068-2-78

Continuous exposure to damp heat (in storage) : Cab: 56 days, 93 % RH, 40  $^{\circ}\text{C}$  conforming to IEC 60068-2-78

Continuous exposure to damp heat (in storage) : Db: 6 days, 95 % RH, 55  $^{\circ}\text{C}$  conforming to IEC 60068-2-30

conforming to IEC 60068-2-30 Exposure to cold (in operation) : Ad: - 25 °C conforming to IEC 60068-2-1

Exposure to cold (in storage): Ab: - 25 °C conforming to IEC 60068-2-1 Exposure to dry heat (in operation): Bd: 70 °C conforming to IEC 60068-2-2 Exposure to dry heat (in storage): Bb: 70 °C conforming to IEC 60068-2-2

Salt mist (in operation): Kb/2: 6 days conforming to IEC 60068-2-52

Temperature variation with specified variation rate (in storage) : Nb: - 25 °C to 70 °C,

5 °C/min conforming to IEC 60068-2-14

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.300 cm
Package 1 Width	15.000 cm
Package 1 Length	21.100 cm
Package 1 Weight	525.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.700 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	80
Package 3 Height	50.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	58.136 kg

# Sustainability Green Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Mercury Free



Rohs Exemption Information

Yes

## **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information