Product datasheet

Specification





iPRD8 modular surge arrester - 1P - 350V

A9L08100

Price: 879.74 ZAR

Main

Range Of Product	Acti9
Product Name	Acti9 iPRD
Product Or Component Type	Surge arrester with pluggable cartridge
Device Short Name	iPRD8
Device Application	Distribution
Standards	EN 61643-11:2012 IEC 61643-11:2011
Product Certifications	CE
Quality Labels	NF KEMA-KEUR
Poles Description	1P
Remote Signalling	Without
Surge Arrester Type	Electrical distribution network
Earthing System	TN-C IT 230

Complementary

Surge Arrester Class Type	Type 2 + 3
Surge Arrester Technology	MOV
[Ue] Rated Operational Voltage	230/400 V AC (+/- 10 %) at 50/60 Hz
[In] Nominal Discharge Current	Common mode: 2.5 kA (L/PE) Common mode: 2.5 kA (N/PE)
[Imax] Maximum Discharge Current	Common mode: 8 kA L/PE
[Uoc] Open Circuit Voltage	10 kV type 3 common mode L/PE
[Uc] Maximum Continuous Operating Voltage	Common mode: 350 V L/PE Common mode: 350 V N/PE
Maximum [Up] Voltage Protection Level	Common mode <1 kV type 2 L/PE Common mode <1 kV type 3 L/PE
[Ut] Temporary Overvoltage	337 V L/N 5 s withstand 1200 V N/PE 200 ms safe failure mode
Disconnector Device Type	Associated circuit breaker iC60L 10 A curve C - Icu 25 kA Associated circuit breaker IC60N 10 A curve C - Icu 10 kA Associated circuit breaker iC60H 10 A curve C - Icu 15 kA Associated fuse gG 25 A - Icu 15 kA Associated fuse gG 80 A - Icu 50 kA
Mounting Mode	Clip-on (DIN rail)

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



9 Mm Pitches	2	
Height	85 mm	
Width	18 mm	
Depth	69 mm	
Net Weight	0.11 kg	
Colour	White (RAL 9003)	
[lpe] Ground Residual Current	0.003 mA 0.6 mA	
Connections - Terminals	Tunnel type terminal (downside) 2.535 mm² Tunnel type terminal (upside) 2.535 mm²	
Tightening Torque	2.5 N.m	

Environment

Ik Degree Of Protection	IK03 conforming to IEC 62262
Relative Humidity	595 %
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-2560 °C
Ambient Air Temperature For Storage	-4085 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	7.2 cm
Package 1 Length	9.2 cm
Package 1 Weight	129 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.5 cm
Package 2 Width	10 cm
Package 2 Length	28 cm
Package 2 Weight	1.635 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	108
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	15.229 kg

Contractual warranty

Warranty 18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information