Product datasheet

Specification





variable speed drive ATV310. 3 kW. 4 hp. 380...460 V. 3 phase

ATV310HU30N4E

Price: 11,110.45 ZAR

Main

Range Of Product	Easy Altivar 310					
Product Or Component Type	Variable speed drive					
Product Specific Application	Simple machine					
Assembly Style	With heat sink					
Device Short Name	ATV310					
Network Number Of Phases	Three phase					
[Us] Rated Supply Voltage	380460 V - 1510 %					
Motor Power Kw	3 kW for heavy duty 4 kW for normal duty					
Motor Power Hp	4 hp for heavy duty 5 hp for normal duty					
Noise Level	50 dB					

Complementary

Quantity Per Set	Set of 1					
Emc Filter	Without EMC filter					
Type Of Cooling	Integrated fan					
Communication Port Protocol	Modbus					
Connector Type	RJ45 (on front face) for Modbus					
Physical Interface	2-wire RS 485 for Modbus					
Transmission Frame	RTU for Modbus					
Transmission Rate	4800 bit/s 9600 bit/s 19200 bit/s 38400 bit/s					
Number Of Addresses	1247 for Modbus					
Communication Service	Read holding registers (03) 29 words Write single register (06) 29 words Write multiple registers (16) 27 words Read/write multiple registers (23) 4/4 words Read device identification (43)					
Line Current	11.1 A at 380 V (heavy duty) 14.2 A at 380 V (normal duty) 9.2 A at 460 V (heavy duty) 11.6 A at 460 V (normal duty)					
Apparent Power	7.3 kVA at 460 V (heavy duty) 9.3 kVA at 460 V (normal duty)					

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

5 kA (heavy duty) 5 kA (normal duty)							
7.1. A heavy duty							
7.1 A heavy duty 8.9 A normal duty							
10.7 A during 60 s (heavy duty) 9.8 A during 60 s (normal duty)							
90.8 W, at In (heavy duty) 120.4 W, at In (normal duty)							
0.5400 Hz							
4 kHz							
212 kHz adjustable							
120 for asynchronous motor							
170200 % of nominal motor torque depending on drive rating and type of motor							
Up to 150 % of nominal motor torque with braking resistor Up to 70 % of nominal motor torque without braking resistor							
Voltage/frequency ratio (V/f) Voltage/frequency ratio - Energy Saving, quadratic U/f Sensorless vector control (SVC)							
Adjustable							
380460 V three phase							
Terminal, clamping capacity: 1.54 mm², AWG 16AWG 12 (L1, L2, L3, PA/+, PB, U, V, W)							
1.21.4 N.m							
Electrical between power and control							
Internal supply for reference potentiometer: 5 V (4.755.25 V)DC, <10 mA with overload and short-circuit protection Internal supply for logic inputs: 24 V (20.428.8 V)DC, <100 mA with overload and short-circuit protection							
1							
Configurable current Al1 020 mA 250 Ohm Configurable voltage Al1 010 V 30 kOhm Configurable voltage Al1 05 V 30 kOhm							
4							
Programmable LI1LI4 24 V 1830 V							
Negative logic (sink), > 16 V (state 0), < 10 V (state 1), input impedance 3.5 kOhm Positive logic (source), 0< 5 V (state 0), > 11 V (state 1)							
10 ms for analogue input 20 ms, tolerance +/- 1 ms for logic input							
+/- 0.3 % of maximum value for analogue input							
1							
AO1 software-configurable voltage: 010 V AC 010 V 00.02 A, impedance: 470 Ohm, resolution 8 bits AO1 software-configurable current: 020 mA, impedance: 800 Ohm, resolution 8 bits							
2							
Logic output LO+, LO- Protected relay output R1A, R1B, R1C 1 C/O							
5 mA at 24 V DC for logic relay							
2 A at 250 V AC on inductive load cos phi = 0.4 L/R = 7 ms for logic relay 2 A at 30 V DC on inductive load cos phi = 0.4 L/R = 7 ms for logic relay 3 A at 250 V AC on resistive load cos phi = 1 L/R = 0 ms for logic relay 4 A at 30 V DC on resistive load cos phi = 1 L/R = 0 ms for logic relay							

Acceleration And Deceleration Ramps	Linear from 0999.9 s S U					
Braking To Standstill	By DC injection, <30 s					
Protection Type	Line supply overvoltage Line supply undervoltage Overcurrent between output phases and earth Overheating protection Short-circuit between motor phases Against input phase loss in three-phase Thermal motor protection via the drive by continuous calculation of I²t					
Frequency Resolution	Analog input: converter A/D, 10 bits Display unit: 0.1 Hz					
Time Constant	20 ms +/- 1 ms for reference change					
Operating Position	Vertical +/- 10 degree					
Height	184 mm					
Width	140 mm					
Depth	151 mm					
Net Weight	1.8 kg					
Supply Frequency	50/60 Hz +/- 5 %					
Product Destination	Asynchronous motors					

Environment

Electromagnetic Compatibility	Electrical fast transient/burst immunity test - test level: level 4 conforming to IEC 61000-4-4 Electrostatic discharge immunity test - test level: level 3 conforming to IEC 61000-4-2					
	Immunity to conducted disturbances - test level: level 3 conforming to IEC 61000-4-6 Radiated radio-frequency electromagnetic field immunity test - test level: level 3 conforming to IEC 61000-4-3					
	Voltage dips and interruptions immunity test conforming to IEC 61000-4-11					
	Surge immunity test - test level: level 3 conforming to IEC 61000-4-5					
Standards	IEC 61800-3					
Product Certifications	CE					
	EAC					
	KC					
Ip Degree Of Protection	IP20 without blanking plate on upper part					
	IP4X top					
Pollution Degree	2 conforming to IEC 61800-5-1					
Environmental Characteristic	Dust pollution resistance class 3S2 conforming to IEC 60721-3-3					
	Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3					
Shock Resistance	15 gn conforming to IEC 60068-2-27 for 11 ms					
Relative Humidity	595 % without condensation conforming to IEC 60068-2-3					
	595 % without dripping water conforming to IEC 60068-2-3					
Ambient Air Temperature For Storage	-2570 °C					
Ambient Air Temperature For	-1055 °C without derating					
Operation	$5560~^{\circ}\text{C}$ protective cover from the top of the drive removed with current derating $2.2~\%$ per $^{\circ}\text{C}$					
Operating Altitude	<= 1000 m without derating					

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Package 1 Height	19.000 cm
Package 1 Width	18.500 cm
Package 1 Length	23.000 cm
Package 1 Weight	2.100 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	2
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	4.776 kg



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information

Yes


Certifications & Standards


Reach Regulation	REACh Declaration					
Eu Rohs Directive	Compliant with Exemptions					
China Rohs Regulation	China RoHS declaration					
Environmental Disclosure	Product Environmental Profile					
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins					
Circularity Profile	End of Life Information					

ATV310HU30N4E

Dimensions Drawings

Dimensions





Dimensions in mm

а	b	С	G	Н	H1	Ø	For screws
140	171	151	126	157	184	5	M4

Dimensions in in.


а	b	С	G	Н	H1	Ø	For screws
5.51	6.73	5.94	4.96	6.18	7.24	0.20	M4

ATV310HU30N4E

Mounting and Clearance


Mounting Recommendations

Clearance




Mounting Types

Mounting Type A




Mounting Type B



Remove the protective cover from the top of the drive.

Connections and Schema

Three-Phase Power Supply Wiring Diagram



A1: Drive

KM1 : Contactor (only if a control circuit is needed)

P1: 2.2 kΩ reference potentiometer. This can be replaced by a 10 kΩ potentiometer (maximum).

Q1 : Circuit breaker

R: Braking resistor (optional)

(1) Negative logic (Sink)

(2) Positive logic (Source) (factory set configuration)

(3) 0...10 V or 0...20 mA

(4) Line choke three-phase (optional)