Product datasheet

Specifications





Redundant processor module. Modicon M580. HSBY Level 2. Remote

BMEH582040

Price: 177,037.09 ZAR

Main

Range Of Product	Modicon M580
Product Or Component Type	Redundant processor module

Complementary

Number Of Racks	1
Application Specific I/O	Counter
	Accurate time stamping
	Serial link
	HART
	Motion control
	SSI encoder
Checks	Process control
Control Channels	Programmable loops
Integrated Connection Type	1 Ethernet TCP/IP for service port
	2 Ethernet TCP/IP for device network
	USB type mini B
	1 Ethernet for HSBY port
Number Of Remote I/O Station	8 - 2 rack(s) per X80 remote drop
Number Of Distributed Equipment	64
Communication Module	2 Ethernet communication module
Processor Capacity	8 AS-Interface module
Communication Service	DIO scanner
	RIO scanner
Memory Description	Expandable flash, 4 GB for data storage
	Integrated RAM, 10 kB for system memory
	Integrated RAM, 8 MB for program
	Integrated RAM, 768 kB for data
Application Structure	1 periodic fast task
	i cyclic/periodic master task
Cybersecurity	Achilles certified
	DoS prevention
	IPSec
	SNMP logging
	Syslog protocol support
	Transport layer security
	Audit trail
	Embedded firewall
	Firmware signature
	Password protection
	Port hardening
	Secure communiction (HTTPS)
	Security log
Number Of Instructions Per Ms	7.5 Kinst/ms 65 % Boolean + 35 % fixed arithmetic

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"

Current Consumption	270 mA at 24 V DC
Mtbf Reliability	650000 H
Marking	CE

Environment

Vibration Resistance	3 gn
Shock Resistance	30 gn
Ambient Air Temperature For Operation	060 °C
Ambient Air Temperature For Storage	-4085 °C
Operating Altitude	02000 m 20005000 m with derating factor
Relative Humidity	595 % at 55 °C without condensation
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Supply	Internal power supply via rack
Status Led	 1 LED (green) processor running (RUN) 1 LED (red) processor or system fault (ERR) 1 LED (red) I/O module fault (I/O) 1 LED (green) download in progress (DL) 1 LED (green/red) ETH MS (Ethernet port configuration status) 1 LED (green/red) ETH MS (Ethernet network status) 1 LED (green) peer processor running (REMOTE RUN) 1 LED (green) processor ID set to A (A) 1 LED (green) processor acting as Primary (PRIM) 1 LED (green) I/O values overrided by user (FORCED IO) 1 LED (green) Hot standby link status (Hsby Diag)
Net Weight	0.849 kg

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.800 cm
Package 1 Width	17.800 cm
Package 1 Length	25.000 cm
Package 1 Weight	883.000 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	5.795 kg

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Mercury Free


Rohs Exemption Information
 Yes

Certifications & Standards


Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

Dimensions Drawings

CPU Module Only



Modules Mounted on Racks




a: additional space below the rack to accommodate the height of the CPU. For an X Bus rack, the value is 30.9 mm (1.217 in.); for an Ethernet rack, the value is 29.49 mm (1.161 in.).

b: the height of the rack. For an X Bus rack, the height is 103.7 mm (4.083 in.); for an Ethernet rack, the height is 105.11 mm (4.138 in.).

c: the height of the main local rack, 134.6 mm (5.299 in.)

Modules and Cables Mounted in an Enclosure



a: enclosure depth: 135 mm (5.315 in.)

b: wiring + module depth: > 146 mm (5.748 in.)

c: wiring + module + DIN rail depth: > 156 mm (6.142 in.) d: rack height: for an X Bus rack 103.7 mm (4.083 in.); for an Ethernet rack, 105.11 mm (4.138 in.)

e: module height: 134.6 mm (5.299 in.)