# **Product datasheet**

Specification





# TeSys K - differential thermal overload relays - 0.36...0.54 A - class 10A

LR2K0304

Price: 814.92 ZAR

#### Main

Range	TeSys
Product Name	TeSys LRK
Product Or Component Type	Differential thermal overload relay
Device Short Name	LR2K
Relay Application	Motor protection
Product Compatibility	LP1K LC7K LP4K LC1K
Network Type	AC DC
Thermal Overload Class	Class 10A conforming to IEC 60947-4-1
Thermal Protection Adjustment Range	0.360.54 A
[Ui] Rated Insulation Voltage	Power circuit: 690 V conforming to BS 4941 Power circuit: 690 V conforming to IEC 60947 Power circuit: 750 V conforming to VDE 0110 group C Power circuit: 600 V conforming to CSA C22.2 No 14

### Complementary

Network Frequency	<= 400 Hz
Mounting Support	Under contactor Plate, with specific accessories Rail, with specific accessories
Auxiliary Contact Composition	1 NO + 1 NC
[Ith] Conventional Free Air Thermal Current	6 A for signalling circuit
[Ue] Rated Operational Voltage	<= 690 V for power circuit 690 V AC AC-15 for signalling circuit 250 V DC DC-13 for signalling circuit
Associated Fuse Rating	6 A gG for signalling circuit conforming to VDE 0660 6 A gG for signalling circuit conforming to IEC 60947
[Uimp] Rated Impulse Withstand Voltage	6 kV
Power Dissipation Per Pole	2 W
Phase Failure Sensitivity	Yes conforming to IEC 60947-4-1
Local Signalling	Trip indicator (yellow)
Control Type	Red push-button: trip test function Blue push-button: stop and manual reset selector switch: manual or automatic reset

Excluding VAT and subject to change. Please check with your local distributor through "Where to buy"



Connections - Terminals	Screw clamp terminals 1 cable(s) 1.54 mm²solid Screw clamp terminals 2 cable(s) 1.54 mm²solid Screw clamp terminals 1 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 2 cable(s) 0.754 mm²flexible without cable end Screw clamp terminals 1 cable(s) 0.342.5 mm²flexible with cable end Screw clamp terminals 2 cable(s) 0.341.5 mm²flexible with cable end
Tightening Torque	1.3 N.m - on screw clamp terminals - with screwdriver Philips No 2 1.3 N.m - on screw clamp terminals - with screwdriver flat Ø 6 mm 1.3 N.m - on screw clamp terminals - with screwdriver pozidriv No 2
Height	58 mm
Width	45 mm
Depth	65 mm
Net Weight	0.145 kg

## **Environment**

Standards	IEC 60947 NF C 63-650 VDE 0660 BS 4941
Product Certifications	UL CSA UKCA
Protective Treatment	TC conforming to IEC 60068 TC conforming to DIN 50016
Ip Degree Of Protection	IP2X conforming to IEC 60529
Ambient Air Temperature For Operation	-2055 °C without derating conforming to IEC 60947 -3060 °C with derating conforming to IEC 60947
Ambient Air Temperature For Storage	-4070 °C
Operating Altitude	2000 m without derating
Fire Resistance	850 °C conforming to IEC 60695-2-1
Flame Retardance	V1 conforming to UL 94 Requirement 2 conforming to NF F 16-101 Requirement 2 conforming to NF F 16-102
Mechanical Robustness	Shocks NO contact: 10 Gn for 11 ms conforming to IEC 60068-2-27 Shocks NC contact: 10 Gn for 11 ms conforming to IEC 60068-2-27 Vibrations NO contact: 2 Gn, 5300 Hz conforming to IEC 60068-2-6 Vibrations NC contact: 2 Gn, 5300 Hz conforming to IEC 60068-2-6

# **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	7.2 cm
Package 1 Length	4.8 cm
Package 1 Weight	156.0 g
Unit Type Of Package 2	S02
Number Of Units In Package 2	41
Package 2 Height	15.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm

Package 2 Weight 6.742 kg

## **Contractual warranty**

Warranty 18 months

## Sustainability Screen Premium

**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

#### Well-being performance



Mercury Free



Rohs Exemption Information

Yes

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration  Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information

19 Apr 2024